

LED HighBay

Accessories

Accessory Part Number Matrix

XXX (product)	X (family)	XX (part)
HBA - High Bay Accessory	C - Cord M - Mounting S - Sensor J - Junction	01- 19 - Cords 20- 39 - Mounting 40- 59 - Sensors 60- 69 - Junction



Cord Accessories

IMAGE	MAX VOLTAGE	CURRENT CAPACITY	DESCRIPTION	ORDERING CODE	QTY/ CASE*	ACCESSORY USE
01	120V	15A	15A 120V L5-15P PLUG 2' BLK CORD WP TWIST CONNECT	HBAC01	10	For 120 volts application. This NEMA L5-15P Plug - twist connects with L5-15R receptacle. Other end easily connects with Twist connect of High Bay
03	277V	15A	15A 277V L7-15P PLUG 2' BLK CORD WP TWIST CONNECT	HBAC03	10	For 277 volts application. This NEMA L7-15P Plug - twist connects with L7-15R receptacle. Other end easily connects with Twist connect of High Bay
05	120-277V	15A	15A 120-277V 3 WIRES 10' BLK CORD WP TWIST CONNECT	HBAC05	10	For 120V or 277 volts application. Cord is 10' long. Length helps to install High bay away from power. 3 wires connected to junction box. Other end connects with Twist connect of High Bay
06	120-277V	15A	15A 120-277V 3 WIRES 10' WHT CORD WP TWIST CONNECT	HBAC06	10	For 120V or 277 volts application. Cord is 10' long. Length helps to install High bay away from power. 3 wires connected to junction box. Other end connects with Twist connect of High Bay



Mounting Accessories

IMAGE	DESCRIPTION	ORDERING CODE	QTY/ CASE*	ACCESSORY USE
20	ROUND HOOK 24X42X60 M10	HBAM20	10	Used with 125W High bay instead of standard Snap hook.
21	ROUND HOOK 29X49X69 M12	HBAM21	10	Used with 185 & 220W High bay instead of standard Snap hook.
22	9" X 9" ALUMINUM SWIVEL YOKE BRACKET BLACK	HBAM22	10	Yoke bracket to help aim light at any angle. (5 settings)
23	9" X 9" ALUMINUM SWIVEL YOKE BRACKET WHITE	HBAM23	10	Yoke bracket to help aim light at any angle. (5 settings)
26	125V SOCKET HUB & JUNCTION BOX 3/4" SNAPHOOK	HBAM26	10	Connects to NEMA L5-15 plug. Cable can be passed through top of socket hub via hole in snaphook. Used to connect High Bay cable to conduit—3/4" threaded pipe.
27	277V SOCKET HUB & JUNCTION BOX 3/4" SNAPHOOK	HBAM27	10	Connects to NEMA L7-15 plug. Cable can be passed through top of socket hub via hole in snaphook. Used to connect High Bay cable to conduit—3/4" threaded pipe.
28	PASS THRU JUNCTION BOX WITH 3/4" SNAPHOOK	HBAM28	10	Opening at top and bottom allow for internal connecting of cable and provide mechanical fixturing support. Top hole includes 3/4" threaded pipe.

