

**SPDXX/RPDXX
WBDXX/WWDXX
(Square and Round Pole Arms)**

Installation: Insert the pole mounting plate inside pole or tenon adapter, aligning the 3 mounting holes in plate with the 3 mounting holes provided on pole. If poles are not pre-drilled, use template #5 as a guide; for wall bracket use template #6; for wall or wood-pole use template #7. Slide threaded rods through top and bottom mounting holes in pole and start to thread the rods into the matching holes in the mounting plate. Three to four full turns is needed. Place one of the enclosed gaskets over threaded rods and against pole.

To mount arm, slide arm over threaded rod using the bolt-guides inside arm. Place remaining gasket over threaded rods and against mounting arm. These arms do not have a taper as the housings with rounded edges incorporate the 2 degree angle.

To mount fixture, align the mounting holes (inside of fixture) with the threaded rods protruding through the end of the arm. Insert threaded rods into fixture, being careful to align gasketing between fixture housing and mounting arm. Install split lockwashers and cap nuts (furnished) on threaded rods and tighten securely. During this process, be sure the fixture is mounted straight on pole. Make wiring connections. Because wiring connections are made in the mounting arm, 60°C wire is allowed for supply leads. **WARNING:** Options are to be installed in the field. DO NOT alter fittings when mounting the fixtures. Recheck all connections and bolts to insure they will not loosen due to vibration.

Pole Mounting for Area Fixtures				
Intended for use with fixtures with rounded edges				
Height=5"	Depth=2"	Length=		
SQUARE POLE	ROUND POLE	(inches)		
SPD04	RPD04	4		
SPD06	RPD06	6		
SPD09	RPD09	9		
SPD12	RPD12	12		

	<div style="border: 1px solid black; padding: 5px; width: fit-content; margin: 0 auto;"> Top view Square pole arm </div> <div style="text-align: right; margin-top: 5px;"> </div>	<div style="border: 1px solid black; padding: 5px; width: fit-content; margin: 0 auto;"> Top view Round pole arm </div> <div style="text-align: right; margin-top: 5px;"> </div>
--	--	---

Wall Mounting for Area Fixtures				
Intended for use with fixtures with rounded edges				
Height=5"	Depth=2"	Length=		
WALL BRACKET	WALL or WOOD-POLE	(inches)		
WBD04	WWD04	4		
WBD06	WWD06	6		
WBD09	WWD09	9		
WBD12	WWD12	12		

<div style="border: 1px solid black; padding: 5px; width: fit-content; margin: 0 auto;"> Wall Bracket (WBD) </div>	<div style="border: 1px solid black; padding: 5px; width: fit-content; margin: 0 auto;"> Wall or Wood-Pole (WWD) </div>
---	--

Order with fixture or as a separate item. Dimensions and specifications on this page are based on the most current available data and are subject to change without notice. [Click here for drilling templates.](#) [Click here for a copy of the instruction sheet.](#)