

# Fluorescent High Bays

## T5 Lamps



## FEATURES


- Ideal replacement for HID high bays
- Multiple lamp configurations available for varying needs and/or applications
- Snap-fit occupancy sensor can significantly reduce energy consumption (field-installable accessory)
- Field-installable lens assembly provides additional shielding and lamp protection (sold as an accessory)
- Ideal for ambient environments that do not exceed 113°F (45°C)
- Ballast disconnect standard
- Lamped fixtures include 4100K lamps

## ORDERING INFORMATION


Catalog Number	UPC	Description	# of Lamps	Wattage	Voltage	Distribution	Uplight	Ballast Type	Lamp Included	Motion Sensor Included	Pallet Qty.	Standard Carton Qty.
IBZT5 4	745977144141	T5 Fluorescent High Bay	4	54	120 - 277	Narrow	Y	Electronic, Program Rapid Start	N	N	48	1
IBZT5 4L	745977147197	T5 Fluorescent High Bay	4	54	120 - 277	Narrow	Y	Electronic, Program Rapid Start	Y	N	48	1
IBZT5 6	745977147432	T5 Fluorescent High Bay	6	54	120 - 277	Narrow	Y	Electronic, Program Rapid Start	N	N	32	1
IBZT5 6L	745977147470	T5 Fluorescent High Bay	6	54	120 - 277	Narrow	Y	Electronic, Program Rapid Start	Y	N	32	1
IBZT5 4L WD	745977147227	T5 Fluorescent High Bay	4	54	120 - 277	Wide	Y	Electronic, Program Rapid Start	Y	N	48	1
IBZT5 6L WD	745977147579	T5 Fluorescent High Bay	6	54	120 - 277	Wide	Y	Electronic, Program Rapid Start	Y	N	32	1

## DIMENSIONS

4 lamp



6 lamp



## ACCESSORIES (Must be ordered separately)

- **SFR 5** 360° Snap-Fit High Bay Sensor (Not for use with door and lens)
- **WGIBZ14** Wireguard for 4-lamp fixture
- **WGIBZ19** Wireguard for 6-lamp fixture
- **DLIBZ14 ACL** Door Frame Kit with .125" Acrylic Lens for 4-lamp fixture
- **DLIBZ19 ACL** Door Frame Kit with .125" Acrylic Lens for 6-lamp fixture
- **IBZACVH** 10' Adjustable Aircraft Cable with V-hook
- **IBZPMP** Single Point Mounting (Pendant Mount)

## FEATURES

- Ideal replacement for HID high bays
- Multiple lamp configurations available for varying needs and/or applications
- Field-installable lens assembly provides additional shielding and lamp protection (sold as an accessory)
- Ballast disconnect standard

## T8 Lamps




## ORDERING INFORMATION


Catalog Number	UPC	Description	# of Lamps	Wattage	Voltage	Distribution	Uplight	Ballast Type	Lamp Included	Motion Sensor Included	Pallet Qty.	Standard Carton Qty.
IBZT8 4	745977147661	T8 Fluorescent High Bay	4	32	120 - 277	Narrow	Y	Electronic, Instant Start, High BF	N	N	48	1
IBZT8 4 WD	745977147692	T8 Fluorescent High Bay	4	32	120 - 277	Wide	Y	Electronic, Instant Start, High BF	N	N	48	1
IBZT8 6	745977147791	T8 Fluorescent High Bay	6	32	120 - 277	Narrow	Y	Electronic, Instant Start, High BF	N	N	32	1
IBZT8 6 WD	745977147845	T8 Fluorescent High Bay	6	32	120 - 277	Wide	Y	Electronic, Instant Start, High BF	N	N	32	1

## DIMENSIONS

4 lamp



6 lamp



## ACCESSORIES (Must be ordered separately)

- **WGIBZ14** Wireguard for 4-lamp fixture
- **WGIBZ19** Wireguard for 6-lamp fixture
- **DLIBZ14 ACL** Door Frame Kit with .125" Acrylic Lens for 4-lamp fixture
- **DLIBZ19 ACL** Door Frame Kit with .125" Acrylic Lens for 6-lamp fixture
- **IBZACVH** 10' Adjustable Aircraft Cable with V-hook
- **IBZPMP** Single Point Mounting (Pendant Mount)