



Search Milwaukee.com

[Home](#) > [Products](#) > [Tools](#) > [Cordless Tools](#) > [M18™ Cordless System](#) > M18™ Cordless 4-1/2" Cut-off / Grinder

M18™ Cordless 4-1/2" Cut-off / Grinder 2680-22

[SHARE](#) [PRINT](#)

Buy Local

Zip Code



[Photos](#) [Videos](#)

The Milwaukee Advantage

The M18™ Cordless 4-1/2" Cut-off / Grinder provides speed, durability and ease-of-use to the industrial user. Built with a Milwaukee® 4-pole motor, the 2680-22 delivers maximum power when cutting or grinding. The 2680-22 is the only cordless cut-off / grinder in the market to provide the user-preferred paddle switch for comfort and ease-of use when operating in various positions. L-shape intake vents protect the cut-off / grinder by keeping harmful debris from entering the tool and damaging internal components.

Features

Milwaukee 4-Pole Motor- Delivers maximum power when cutting or grinding

Overload Protection- Prevents damage to the tool and battery in abusive situations

Debris Baffles - L-shape vents keep debris from entering the tool and damaging internal components to help increase tool life.

Tool Free, Burst Resistant Guard- Allows for quick, easy guard adjustments. Easy to access and actuate too free guard makes it easier and less time consuming to adjust the guard for various applicatoinis.

Paddle Switch Design- The only cordless cut-off /grinder in the market with a paddle switch design

Up to 35% faster cutting speed

Up to 50% more cuts on a single charge

3-Position Side Handle- Provides optimal Control and Versatility

Specifications

Voltage	18V
RPMs	9,000
Paddle Switch	Yes
Tool Free Guard	Yes
Large Button Spindle Lock	Yes
Position Handle	3
Type 1 Guard	Yes
Type 27 Guard	Yes
Battery	LITHIUM-ION

Related Items

- M18™ XC High Capacity LITHIUM-ION Battery
- Grinding Wheel 4-1/2 in. x 1/4 in. x 7/8 in. (Type 27)
- M18™ LITHIUM-ION Battery Charger

[+ More Related Items](#)

Related Articles

[Milwaukee® Introduces New M18 Cordless 4-1/2" Cut-Off / Grinder](#)



Service Info

- [Manual](#)
- [B96A](#)
- [Parts Diagram](#)
- [B96A](#)

Tool Weight	5.9 lbs
Shipping Weight	13.25 lbs
Standard Equipment	2680 4-1/2" Cut-off Grinder (2) 18V XC High Capacity LITHIUM- ION Batteries 1-Hour Charger Type 1 Guard Type 27 Guard, Type 1 Cut-Off Wheel, Spanner Wrench Side Handle Contractor Bag

Includes

2680 4-1/2" Cut-off Grinder
(2) 18V XC High Capacity LITHIUM-ION Batteries
1-Hour Charger
Type 1 Guard
Type 27 Guard,
Type 1 Cut-Off Wheel,
Spanner Wrench
Side Handle
Contractor Bag

