

# Installation Accessories

## Handles



Cable Range	Poly Handle w/Bushing*	NPT	Poly Handle w/NPT***
.51 - .75	22-6A013-25P+	1"	22-6A013-1***
.67 - .98	22-6A013-32P+		
.95 - 1.26	22-6A013-40P+		

+ ATEX rated for use in Zone 1/21, not listed for Class I or II, Division 2.  
 \*\*\* For use in Class I or II, Division 2 or Zone 1/21 depending on fitting used. Fitting manufactured by others.

## Angles



Nylon 30° Angle

22-6A027

DXN accessories are not returnable.

## NPT Guidelines

Cable Range	NPT
.660 - 1.000	1"

NPT sizes are determined by the cable diameter and third party cord grip.

## Wall Boxes



Cable Range	Poly 70°++ Wall Box	NPT	Poly 30°* Wall Box	Poly 30°*** Wall Box	Poly 70°*** Alum Wall Box
.629 - .984	22-6AB58	1/2"	-	-	22-6A058-12
		3/4"	-	-	22-6A058-34
		1"	22-6A023-1-T	22-6A023-1-B	22-6A058-1
		1 1/4"	-	-	22-6A058-114
		1 1/2"	-	-	22-6A058-112

+ Interior volume with receptacle installed.  
 ++ Poly cord grip is located on the top of box. For bottom cord entry, rotate the box 180°.  
 \* NPT thread on top.  
 \*\* NPT thread on bottom.  
 \*\*\* NPT is drilled on top of aluminum box as standard. For NPT on side only, add an "L" suffix. To switch from top to bottom or left to right the box can be rotated 180°.

## Accessory Spotlight

### Finger Drawplates



Finger drawplates are recommended for easier connector closure on cord to cord assemblies.

## Miscellaneous Accessories



\* Set of Two (2)



For Male Devices Only



Receptacle + Lockout Pin

Finger Drawplates	Protective Cap	Receptacle + Lockout Pin
61-6A346	22-6A426	LP-843

\* Recommended for cord to cord assembly applications, for easier connector closure.  
 + Requires Padlockable Pawl option (-843) on receptacle.

## HP rated DXN60

### DXN60 Horsepower Ratings

AMPS	VAC (Max) @ 60 Hz	Phases	HP Rating
60	120V	1Ø	2 hp
60	240V	3Ø	7.5 hp
60	480V	3Ø	20 hp
60	600V	3Ø	20 hp



• HP ratings are based on CSA certification

## Order Example

A typical order should include an inlet part number, a receptacle part number **AND** the matching handles, angles or other required accessories.



Male Inlet with Handle (Plug)  
 22-68043 + 22-6A013-32P



Female Receptacle with Wall Box  
 22-64043 + 22-6A023-1-T