



# 7/8" MIN Series Size I Accessories

## 2, 3 & 4 Conductor MIN Series Size I Accessory Cables



100' Cables | Raw Cable Spools

# of Conductors	Color Code	Wire AWG	Voltage Rating	Features	Jacket Color	Part Number	
						100' Cable	Spool
2	North American White Black	16 AWG	600V	PVC STOOW 9.4mm OD (0.37" OD)	Yellow	MIN-2CBL-C	10A0001-*
					Black	MIN-2CBL-C-B	10A0001-*
3	North American Green/Yellow Black White	16 AWG	600V	PVC STOOW 10mm OD (0.39" OD)	Yellow	MIN-3CBL-C	10B0001-*
					Black	MIN-3CBL-C-B	10BB001-*
				PUR AWM 10mm OD (0.39" OD)	Yellow	MINP-3CBL-C	10BP001-*
					Black	MINP-3CBL-C-B	10BP001-*
		TPE SEOOW 10mm OD (0.39" OD)	Yellow	MINW-3CBL-C	10BW001-*		
			Black	MINW-3CBL-C-B	10BWB01-*		
		18 AWG	300V	PVC SJTOOW 8.5mm OD (0.33" OD)	Yellow	MIN-3CBLX-C	10BX001-*
					Black	MIN-3CBLX-C-B	10BXB01-*
	North American Auto Color Code Green/Yellow Red/Black Red/White	16 AWG	600V	PVC STOOW 10mm OD (0.39" OD)	Yellow	MIN-3ACBL-C	10L0001-*
		18 AWG	300V	PVC SJTOOW 8.5mm OD (0.33" OD)	Yellow	MIN-3ACBLX-C	10LX001-*
	European Green/Yellow Brown Blue	18 AWG	300V	PVC AWM 7.4mm OD (0.29" OD)	Yellow	MINE-3CBLX-C	10BXE01-*
					Black	MINE-3CBLX-C-B	10BXE01-*
European Cenelec Black Brown Blue	18 AWG	600V	PVC AWM 7.4mm OD (0.29" OD)	Yellow	MINC-3CBLX-C	30BX001-*	
				Black	MINC-3CBLX-C-B	30BX001-*	
4	North American Black White Red Green/Yellow	16 AWG	600V	PVC STOOW 10.8mm OD (0.42" OD)	Yellow	MIN-4CBL-C	10C0001-*
					Black	MIN-4CBL-C-B	10CB001-*
		18 AWG	300V	PVC AWM 7.4mm OD (0.29" OD)	Yellow	MIN-4CBLX-C	10CX001-*
					Black	MIN-4CBLX-C-B	10CX001-*
	European Cenelec Brown White Blue Black	18 AWG	600V	PVC AWM 7.4mm OD (0.29" OD)	Yellow	MINC-4CBLX-C	30CX001-*
			300V	PUR AWM 7.4mm OD (0.29" OD)	Yellow	MINCP-4CBLX-C	30CXP01-*
		TPE AWM 7.4mm OD (0.29" OD)		Yellow	MINCW-4CBLX-C	30CWX01-*	
			Black	MINCW-4CBLX-C-B	30CWX01-*		

MIN Series Size I Cordsets

\* Standard raw spool lengths are 0250, 0500, 0750 & 1000 feet. Consult factory for other lengths.

Cable Construction subject to change without notice.

Lengths in feet. Standard cable length is 100 feet. Consult factory for other lengths.