

Digital Multimeter

2216-20

**AVAILABLE
FALL 2010**

Specifications:

Voltage Range	6mV to 600V AC 600mV to 600V DC
Safety Rating	CAT III 600V
TRMS	YES
Current Range	0.040A to 10.00A AC/DC

Includes Electrical Test Lead Set, (2) AA Batteries, Manual



LASER TEMP-GUN™

2266-20

Specifications:

Temperature Range	-20° F to 932° F (-30° C to 500° C)
Base Accuracy	1.50%
Distance to Spot	12 to 1
Contact Temperature Range	-22° F to 842° F (-30° C to 450° C)

Includes (3) AA Batteries, Manual



Digital Multimeter

2217-20

Specifications:

Voltage Range	6mV to 600V AC 600mV to 600V DC
Lo-Z	YES
Safety Rating	CAT III 600V
TRMS	YES
Current Range	0.040A to 10.00A AC/DC
Contact Temperature Range	-40° F to 752° F (-40° C to 400° C)

Includes Electrical Test Lead Set, Dual Banana Thermocouple, (2) AA Batteries, Manual



Laser Distance Meter

2280-20

Specifications:

Distance Range	0.16' (0.05m) to 197' (60m)
Base Accuracy	± 0.059" (± 1.5 mm)
Display Resolution	000' 00 in 1/8, 000.00', 00.000 m
Arithmetic Functions	YES

Includes (2) AAA batteries, Carrying Case, Manual



400 Amp Clamp Meter

2235-20

**AVAILABLE
FALL 2010**

Specifications:

Current Range	400A AC
Voltage Range	600V AC/DC
Safety Rating	CAT III 600V
TRMS	YES

Includes Electrical Test Lead Set, (2) AA Batteries, Manual

405.759



Voltage Detector with Work Light

2201-20

Specifications:

Voltage Range	90 to 600V AC
Safety Rating	CAT III 600V
AC Volts	600
Scan for AC Electrical	YES

Includes (1) AAA Battery, Pocket Clip, Manual



Clamp Meter for HVAC/R

2236-20

Specifications:

Current Range	600A AC
Voltage Range	600V AC/DC
Safety Rating	CAT III 600V
Contact Temperature Range	-40° F to 752° F (-40° C to 400° C)
TRMS	YES

Includes Electrical Test Lead Set, Dual Banana Thermocouple, (2) AA Batteries, Manual



Voltage Detector with LED

2202-20

**AVAILABLE
FALL 2010**

Specifications:

Voltage Range	50 to 1,000V AC
Safety Rating	CAT IV 1,000V
LED Light	YES
Scan for AC Electrical	YES

Includes (2) AAA Batteries, Manual



Clamp Meter

2237-20

Specifications:

Current Range	600A AC/DC
Voltage Range	600V AC/DC
Safety Rating	CAT III 600V
TRMS	YES

Includes Electrical Test Lead Set, (2) AA Batteries, Manual



Electrical Test Lead Set 49-77-1001

Industrial Test Lead Set 49-77-1003

Industrial Test Probes 49-77-1004

Industrial Alligator Clips 49-77-1005

Fits models 2205-20, 2206-20, 2207-21, 2216-20, 2217-20, 2235-20, 2236-20, 2237-20, 2238-21 and 2239-21

Thermocouple (Dual Banana) 49-77-2001

Fits models 2206-20, 2217-20, 2236-20 and 2238-21

Thermocouple (K-type) 49-77-2002

Fits models 2266-20, 2276-21 and 2277-21

Magnetic Meter Holder 49-77-3001

Fits models 2207-21, 2217-20

Meter Cases 48-55-0175, 48-55-0180 (Large)