


		REV-00
Date: August 15, 2014		M.FW.140.A2

Flat Washers, Metric, A2 Stainless Steel

The information below lists the required dimensional, chemical and physical characteristics of the fasteners in this purchase order. If the order received does not meet these requirements, it may result in a supplier corrective action request, which could jeopardize your status as an approved vendor. Unless otherwise specified, all referenced consensus standards must be adhered to in their entirety.



Thread Size	A		B		C		
	Inside Diameter		Outside Diameter		Thickness		
	Min./Nom.	Max.	Max./Nom.	Min.	Nom.	Max.	Min.
1.6	1.7	1.84	4	3.7	0.3	0.35	0.25
2	2.2	2.34	5	4.7	0.3	0.35	0.25
2.5	2.7	2.84	6	5.7	0.5	0.55	0.45
3	3.2	3.38	7	6.64	0.5	0.55	0.45
3.5	3.7	3.88	8	7.64	0.5	0.55	0.45
4	4.3	4.48	9	8.64	0.8	0.9	0.7
5	5.3	5.48	10	9.64	1	1.1	0.9
6	6.4	6.62	12	11.57	1.6	1.8	1.4
7	7.4	7.62	14	13.57	1.6	1.8	1.4
8	8.4	8.62	16	15.57	1.6	1.8	1.4
10	10.5	10.77	20	19.48	2	2.2	1.8
12	13	13.27	24	23.48	2.5	2.7	2.3
14	15	15.27	28	27.48	2.5	2.7	2.3
16	17	17.27	30	29.48	3	3.3	2.7
18	19	19.33	34	33.38	3	3.3	2.7
20	21	21.33	37	36.38	3	3.3	2.7
22	23	23.33	39	38.38	3	3.3	2.7
24	25	25.33	44	43.38	4	4.3	3.7
26	27	27.33	50	49.38	4	4.3	3.7
27	28	28.33	50	49.38	4	4.3	3.7
30	31	31.39	56	55.26	4	4.3	3.7
33	34	34.62	60	58.8	5	5.6	4.4
36	37	37.62	66	64.8	5	5.6	4.4
39	40	40.62	72	70.8	6	6.6	5.4
42	43	43.62	78	76.8	7	8	6
45	46	46.62	85	83.6	7	8	6
48	50	50.62	92	90.6	8	9	7
50	52	52.74	92	90.6	8	9	7
52	54	54.74	98	96.6	8	9	7
56	58	58.74	105	103.6	9	10	8
64	66	66.74	115	113.6	9	10	8