

Product Search Part #, Name or Category  [Cross Reference](#)

Products

[PRODUCTS](#)

ELECTRICAL

- [Polaris™](#)
- [Tools & Hardware](#)
- [Connectors](#)
- [Firestop](#)
- [Grounding](#)
 - [Ground Clamps](#)
 - [Conduit Hubs](#)
 - [Ground Rod Clamps](#)
 - [Ground Rod Plate](#)
 - [Ground Bars](#)
 - [Ground Connectors](#)
 - [C Taps](#)
 - [Pigtails](#)
 - [Grounding Hardware](#)
 - [Bonding Connectors](#)

- [Easy-Twist](#)
- [Splicing](#)
- [Miniterms](#)
- [Switches](#)
- [DataComm](#)
- [Wire Management](#)

[TORK](#)

[LIGHTING](#)

[POOL & SPA PRODUCTS](#)

Email Newsletter



[Home](#) [Products](#) [Electrical](#) [Grounding](#) [Ground Bars](#) [Ground Bar](#) [Aluminum Neutral Bar](#)

Aluminum Neutral Bar



AL Neutral Bars: Multiple connectors are made from either copper or aluminum bar and can be used in a variety of neutral and grounding applications. Tin plated for low contact resistance and are suitable for use with copper or aluminum conductors.

Combination Connectors: Multiple combination connectors are made from aluminum and are tin-plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Each connector contains a combination of 1/0-14 AWG and 6-14 AWG wire holes.

[Products](#) [Product Documentation](#) [Videos & How-To's](#)

SKU	UPC	Name	Weight	Qty Avail	Price
2-14(12311)	66238100631	ALUMINUM MULTIPLE CONNECTOR, 2-14 AWG,12 HOLES 10 CIRCUITS - NON UL	0.08		
CB-11	66238100901	11 CIRCUIT COMB.CONNECTOR	0.11		
4-14(11111)	66238100607	ALUMINUM MULTIPLE CONNECTOR, 4-14 AWG, 11 HOLES 9 CIRCUITS	0.06		
1012MB	66238100803	225A STACKED NEUTRAL BAR, 4-14 AWG 12 CIRCUITS & 350 MCM - 6 AWG MAIN LUG WITH MTG BASE	0.00		
1012M	66238100801	225A STACKED NEUTRAL BAR, 4-14 AWG 12 CIRCUITS & 350 MCM - 6 AWG MAIN LUG	0.00		
1012	66238100800	225A STACKED NEUTRAL BAR, 4-14 AWG 12 CIRCUITS	0.00		
1012B	66238100802	225A STACKED NEUTRAL BAR, 4-14 AWG 12 CIRCUITS - WITH MTG BASE	0.00		
4-14(12112)	66238100608	ALUMINUM MULTIPLE CONNECTOR, 4-14 AWG, 12 HOLES 10 CIRCUITS	0.06		
CB-120	66238100904	120CIRCUIT COMB.CONNECTOR	1.82		
4-14(14114)	66238100609	ALUMINUM MULTIPLE CONNECTOR, 4-14 AWG, 14 HOLES 12 CIRCUITS	0.07		
4-14(17117)	66238100610	ALUMINUM MULTIPLE CONNECTOR, 4-14 AWG, 17 HOLES 15 CIRCUITS	0.09		
1018M	66238100805	225A STACKED NEUTRAL BAR, 4-14 AWG 18 CIRCUITS & 350 MCM - 6 AWG MAIN LUG	0.00		
1018	66238100804	225A STACKED NEUTRAL BAR, 4-14 AWG 18 CIRCUITS	0.00		
1018B	66238100806	225A STACKED NEUTRAL BAR, 4-14 AWG 18 CIRCUITS - WITH MTG BASE	0.00		
1018MB	66238100807	225A STACKED NEUTRAL BAR, 4-14 AWG 18 CIRCUITS & 350 MCM - 6 AWG MAIN LUG WITH MTG BASE	0.00		
CB-19	66238100902	19 CIRCUIT COMB.CONNECTOR	0.18		
2/0-14(818)	66238100643	ALUMINUM MULTIPLE CONNECTOR, 2/0-14 AWG, 8 HOLES 6 CIRCUITS - NON UL	0.20		

2/0-14(524)	66238100641	ALUMINUM MULTIPLE CONNECTOR, 2/0-14 AWG, 5 HOLES 3 CIRCUITS - NON UL	0.13			
4-14(22122)	66238100611	ALUMINUM MULTIPLE CONNECTOR, 4-14 AWG, 22 HOLES 20 CIRCUITS	0.11			
CB-23	66238100903	23 CIRCUIT COMB.CONNECTOR	0.22			

[Previous](#) [Next](#)