

Product Search Part #, Name or Category  Cross Reference

Products

[Home](#) [Products](#) [Electrical](#) [Polaris™](#) [Insulated Blue](#) [DB/Submersible Multi-Cable Connectors](#) [IPLW SERIES](#)

PRODUCTS

ELECTRICAL

- Polaris™
- Polaris™
- Insulated Blue**
- Insulated Grey
- Insulated
- Non-Insulated
- Tools & Hardware
- Connectors
- Firestop
- Grounding
- Easy-Twist
- Splicing
- Miniterms
- Switches
- DataComm
- Wire Management

TORK

LIGHTING

POOL & SPA PRODUCTS

Email Newsletter

Enter Email Address 

IPLW SERIES



Abrasion and chemical resistant. UV rated. Will not support combustion. Cold temperature rated to -45°C. Suitable for use with aluminum and/or copper conductors. 600 volts. 90°C. Reusable. UL Listed 486D for DB/sub applications.

Products Product Documentation Videos & How-To's

SKU	UPC	Name	Weight	Qty Avail	Price
IPLW3/0-5	66238178933	3/0 - 1/0 AWG FIVE WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	1.08		
IPLW1-5	66238178931	1-2 AWG FIVE WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.49		
IPLW250-5	66238178935	250 MCM - 4/0 AWG FIVE WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	1.06		
IPLW4-5	66238178929	4-6 AWG FIVE WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.35		
IPLW1-4	66238195122	1-2 AWG FOUR WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.39		
IPLW3/0-4	66238195118	3/0 - 1/0 AWG FOUR WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.81		
IPLW4-4	66238195116	4-6 AWG FOUR WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.27		
IPLW250-4	66238195120	250 MCM - 4/0 AWG FOUR WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.84		
IPLW4-6	66238178930	4-6 AWG SIX WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.43		
IPLW3/0-6	66238178934	3/0 - 1/0 AWG SIX WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	1.35		
IPLW1-6	66238178932	1-2 AWG SIX WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.59		
IPLW250-6	66238178936	250 MCM - 4/0 AWG SIX WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	1.28		
IPLW4-3	66238195115	4-6 AWG THREE WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.19		
IPLW1-3	66238195121	1-2 AWG THREE WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.29		
IPLW250-3	66238195119	250 MCM - 4/0 AWG THREE WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.62		
IPLW3/0-3	66238195117	3/0 - 1/0 AWG THREE WIRE POLARIS BLUE (DIRECT BURIAL & SUBMERSIBLE)	0.54		

