



3/4" S&D Black Oxide Drill Bit

48-89-2746



What's Included

(1) 3/4" S&D Black Oxide Drill Bit (48-89-2746)

Where to Buy



Shop Online



Find Local

Milwaukee® S&D Black Oxide drill bits are designed for extreme durability and long life. A specially designed parabolic flute form clears chips fast, while the 3-Flat Secure-Grip™ shank holds the bit firmly in the drill chuck. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Effective for drilling on curved surfaces, Milwaukee® Black Oxide bits require less effort to drill through metal, wood and PVC, and are highly recommended for use with portable drills.

Features

- Fast, accurate drilling: 135° split point tip starts on contact to prevent walking, while the parabolic flute clears chips fast
- Reduced slipping: 3-Flat Secure-Grip™ shank holds the bit firmly in the drill chuck
- Corrosion resistant: Black oxide coating provides lubricity and resists corrosion of the bit
- Versatile: Reduced shank diameter for use in 1/2" chucks

Specifications


Pack Qty	1 Pack
Shank	3-Flat (1/2")
Diameter	.753/4"
Coating	Black Oxide
Length	6"
Flute Length	3"
Size	.7503/4"
Decimal Equivalent	0.75
Application	Metal Wood Plastic

Model Options

Item/Cat #	Size	Flute Length	Length	Pack Qty	
------------	------	--------------	--------	----------	--

48-89-2739	17/32"	3"	6"	1 Pack	Shop Online Find Local
48-89-2740	.5629/16"	3"	6"	1 Pack	Shop Online Find Local
48-89-2741	19/32"	3"	6"	1 Pack	Shop Online Find Local
48-89-2742	.6255/8"	3"	6"	1 Pack	Shop Online Find Local
48-89-2743	21/32"	3"	6"	1 Pack	Shop Online Find Local
48-89-2744	.68711/16"	3"	6"	1 Pack	Shop Online Find Local
48-89-2745	23/32"	3"	6"	1 Pack	Shop Online Find Local
48-89-2746	.7503/4"	3"	6"	1 Pack	Shop Online Find Local
48-89-2747	25/32"	3"	6"	1 Pack	Shop Online Find Local
48-89-2748	.81213/16"	3"	6"	1 Pack	Shop Online Find Local
48-89-2749	27/32"	3"	6"	1 Pack	Shop Online Find Local
48-89-2750	.8757/8"	3"	6"	1 Pack	Shop Online Find Local
48-89-2751	29/32"	3"	6"	1 Pack	Shop Online Find Local
48-89-2752	.93715/16"	3"	6"	1 Pack	Shop Online Find Local

48-89-2753	31/32"	3"	6"	1 Pack	Shop Online Find Local
48-89-2754	1.001"	3"	6"	1 Pack	Shop Online Find Local
48-89-2755	1.061-1/16"	3"	6"	1 Pack	Shop Online Find Local
48-89-2756	1.121-1/8"	3"	6"	1 Pack	Shop Online Find Local
48-89-2757	1.1871-3/16"	3"	6"	1 Pack	Shop Online Find Local
48-89-2758	1.251-1/4"	3"	6"	1 Pack	Shop Online Find Local



© 2017 by Milwaukee Tool. All rights reserved.