



PAR 56, 64



PAR36

HALOGEN

LARGE PAR

aluPAR®

ANSI Code	Product Number	Ordering Abbreviation	Watts (W)	Volts (V)	Base	Centerbeam Candlepower (cp)	Color Temp (K)	Avg Rated Life (hrs)	Bulb	Pkg Qty	Symbols & Footnotes
	56000	aluPAR 56/NSP/300W/230V	300	230	GX16D	70000	2950	2000	PAR56	6	27,76,77
	56001	aluPAR 56/MFL/300W/230V	300	230	GX16D	30000	2950	2000	PAR56	6	26,76,77
	56002	aluPAR 56/WFL/300W/230V	300	230	GX16D	10000	2950	2000	PAR56	6	28,76,77
	56003	aluPAR 56/NSP/300W/120V	300	120	GX16D	68000	2950	2000	PAR56	6	27,76,77
	56004	aluPAR 56/MFL/300W/120V	300	120	GX16D	24000	2950	2000	PAR56	6	26,76,77
	56005	aluPAR 56/WFL/300W/120V	300	120	GX16D	11000	2950	2000	PAR56	6	28,76,77
	56086	aluPAR 56/NSP/500W/120V	500	120	GX16D	96000	2950	4000	PAR56	6	27,76,77
	56213	aluPAR 56/MFL/500W/120V	500	120	GX16D	43000	2950	4000	PAR56	6	26,76,77
	56006	aluPAR 56/WFL/500W/120V	500	120	GX16D	19000	2950	4000	PAR56	6	28,76,77
	56007	aluPAR 64/NSP/500W/120V	500	120	GX16D	110000	2950	2000	PAR64	6	27,76,77
	56008	aluPAR 64/MFL/500W/120V	500	120	GX16D	37000	2950	2000	PAR64	6	26,76,77
	56009	aluPAR 64/WFL/500W/120V	500	120	GX16D	13000	2950	2000	PAR64	6	28,76,77
FFN	56017	aluPAR 64/VNSP/1000W/120V/FFN	1000	120	GX16D	400000	3200	800	PAR64	6	29,76,77
FFP	56010	aluPAR 64/NSP/1000W/120V/FFP	1000	120	GX16D	330000	3200	800	PAR64	6	29,76,77
FFR	56011	aluPAR 64/MFL/1000W/120V/FFR	1000	120	GX16D	125000	3200	800	PAR64	6	26,76,77
FFS	56012	aluPAR 64/WFL/1000W/120V/FFS	1000	120	GX16D	40000	3200	800	PAR64	6	26,76,77

LARGE PAR – OTHER

ANSI Code	Product Number	Ordering Abbreviation	Watts (W)	Volts (V)	Base	Centerbeam Candlepower (cp)	Color Temp (K)	Avg Rated Life (hrs)	Bulb	Pkg Qty	Symbols & Footnotes
	55052	20PAR/36/CAP/WFL	20	12	G53			4000	PAR36	12	
	54499	4515 PAR36 30W	30	6	G53			100	PAR36	12	
	64075	PAR56 12V 300W	300	12	Screw Term				PAR56	6	28
	14974	350PAR56/SP	350	75	MEP		2900	750	PAR56	12	24
	56229	Q4681	450	28	G53	310000		50	PAR46	12	24,29
	56222	Q4559	600	28	G53	600000		100	PAR64	6	24,29
	56223	Q4559X	600	28	G53	765000		100	PAR64	6	24,29
DWE	54500	DWE	650	120	G53		3200	100	PAR36	12	
EXD	56233	EXD/240	1000	240	GX16D	275000	3200	300	PAR64	6	24
EXE	56234	EXE/240	1000	240	GX16D	130000	3200	300	PAR64	6	24
FFN	56214	FFN	1000	120	GX16D	400000	3200	800	PAR64	6	24,29
FFP	56215	FFP	1000	120	GX16D	330000	3200	800	PAR64	6	24,27
FFR	56217	FFR	1000	120	GX16D	125000	3200	800	PAR64	6	24,26
FFS	56216	FFS	1000	120	GX16D	40000	3200	800	PAR64	6	24,28

For the current listing of available products and more complete product information, please visit us at www.sylvania.com