




Grounding

DIRECT BURIAL, HEAVY DUTY & EXTRA HEAVY DUTY GROUND CLAMPS



1. DIRECT BURIAL BRONZE GROUND CLAMPS

CATALOG NO.	UPC NO.	CONDUIT SIZE (INCHES)	GROUND WIRE RANGE	PIECES PER CARTON	SHPG. WT. LBS./100
G-1-S-DB	01008	1/2 - 1	2 stranded	20	28
G-2-S-DB	01009	1 1/4 - 2	2 stranded	10	49

UL Listed for direct burial in earth or concrete. Screws are silicon bronze.

2. HEAVY DUTY BRONZE GROUND CLAMP - DIRECT BURIAL FOR REBAR

CATALOG NO.	UPC NO.	PIPE SIZE (INCHES)	GROUND WIRE MAX.	PIECES PER CARTON	SHPG. WT. LBS./100
G-1-S-DBR	00533	3/8 - 1	2 AWG	20	28

Used to connect bare copper wire to water pipe, ground rods and rebar for bonding. Assembled with copper screws and UL Listed for direct burial in earth and concrete. Can accommodate ground wires up to 2 AWG.

3. EXTRA HEAVY DUTY DIRECT BURIAL GROUND CLAMP

CATALOG NO.	UPC NO.	GROUND WIRE RANGE	PIECES PER CARTON	SHPG. WT. LBS./100
G-1400B	00555	8 stranded - 4/0 stranded	10	45

Suitable for: 3/8 - 1" rebar, 1/2 - 1" water pipe, 1/2 - 1" copper water tubing, 1/2 - 1" ground rod

This incredible ground clamp can handle just about any size ground wire and just about any application. UL Listed for direct burial in earth and concrete, it can be used with rebar, water pipe, copper tubing and ground rods up to 1 inch in diameter. Assembled with tough, stainless steel screws. Will accommodate ground wires from 8 AWG to 4/0 AWG.

4./5. HEAVY DUTY DIRECT BURIAL GROUND CLAMP WITH LAY-IN FEATURE

CATALOG NO.	UPC NO.	GROUND WIRE RANGE	SCREW MATERIAL	PIECES PER CARTON	SHPG. WT. LBS./100
GLC-140DB	00556	8 stranded - 4/0 stranded	stainless steel	10	55
GLC-12 DB	00534	#10 - 2 stranded	silicon bronze	25	31
GLC-12 RDB	00535	#10 - 2 stranded	silicon bronze	25	31

Suitable for: 3/8 - 1" rebar, 1/2 - 1" water pipe, 1/2 - 1" copper water tubing, 1/2 - 1" ground rod

The ultimate ground clamp for large ground wires. This incredible ground clamp can handle just about any size ground wire and just about any application. The lay-in feature provides for the ultimate in flexibility. UL Listed for direct burial in earth and concrete, it can be used with rebar, water pipe, copper tubing and ground rods up to 1 inch in diameter. Screws conveniently pre-assembled. Will accommodate ground wires from 8 AWG to 4/0 AWG.