

A.
System
Overview

Plastic Heat Shrink Tubing Kit Boxes – For Dry Locations

B1.
Cable Ties



B2.
Cable
Accessories

B3.
Stainless
Steel Ties

| Part Number | Part Description | Contents | Std. Pkg. Qty. |
|-------------|--|---|----------------|
| KP-HSTT1 | Heat shrink kit box - plastic case, various sizes. black only. | 35 ea. of 3/32", 1/8" 21 ea. of 3/16", 1/4" 7 ea. of 3/8", 1/2" | 1 |
| KP-HSTT2 | Heat shrink kit box - plastic case, various sizes, various colors. | 35 ea. (5 ea color) 3/32", 1/8" 21 ea. (3 ea color) 3/16", 1/4" 7 ea. (1 ea color) 3/8", 1/2" | 1 |
| KP-HSTTA | Dual Wall Adhesive Lined Thin Wall Heat Shrink: Plastic Kit Box - Black only | 14 ea 3/16" 12 ea 1/4" 10 ea 3/8" 6 ea 1/2" 3 ea 3/4" 2 ea 1" | 1 |

C1.
Wiring
Duct

C2.
Surface
Raceway

C3.
Abrasion
Protection



Heat Shrink Tools and Accessories

C4.
Cable
Management



D1.
Terminals

D2.
Power
Connectors

D3.
Grounding
Connectors

| Part Number | Part Description | Std. Pkg. Qty. | Std. Ctn. Qty. |
|--------------|--|----------------|----------------|
| HSG-115V-650 | Heat gun with temperature range of 650°F (344°C) to 900°F (482°C). | 1 | – |
| HSG-A1 | Shrink tube reflector for tubing up to 3/4" inside diameter. Directs heat around tubing to reduce shrink time. | 1 | 10 |
| HSG-A2 | Shrink tube reflector for tubing up to 1 1/2" inside diameter. Directs heat around tubing to reduce shrink time. | 1 | 10 |
| HSG-A4 | Black polyethylene case stores heat gun, stand, and all three accessories. | 1 | – |
| HSG-P1 | Replacement brush / spring kit. | 1 | 5 |
| HSG-P2 | Replacement switch 20 Amp. | 1 | 5 |
| HSG-P3 | Replacement bearing kit. | 1 | 5 |
| HSG-P7 | Replacement heat element 650°F. | 1 | – |

E1.
Labeling
Systems

E2.
Labels

E3.
Pre-Printed
& Write-On
Markers

E4.
Permanent
Identification

E5.
Lockout/
Tagout
& Safety
Solutions

F.
Index