

COMPRESSION CONNECTORS
Tool and Die Charts
For Connector Series: PT, PTO, PTS
ALUMINUM CONNECTORS

ALUMINUM COMPRESSION CONNECTOR TOOL AND DIE CHART

CONNECTOR SERIES: PT, PTO, PTS

ALUMINUM CONDUCTOR ONLY PT SERIES	ALUMINUM CONDUCTOR ONLY PT SERIES	ALUMINUM OR COPPER CONDUCTOR PTS & PTO SERIES	ALUMINUM OR COPPER CLASS B/C CONDUCTOR SIZE PTS & PTO SERIES	PIN SIZE	MIN. # OF CRIMPS REQUIRED	COPPER COLOR CODE	NSI DIE	NSI/GREENLEE DIE
-	-	PTS6	6 AWG	4 AWG	1	TAN	CD9	KA12-1/0
PT6	6 AWG	-	-	8 AWG	1	-	BG 52	-
-	-	PTS4	4 AWG	4 AWG	1	TAN	CD9	KA12-1/0
PT4	4 AWG	-	-	6 AWG	1	-	BG 52	-
-	-	PTS2	2 AWG	4 AWG	1	TAN	CD9	KA12-1/0
PT2	2 AWG	-	-	4 AWG	1	-	BG 52	-
-	-	PTS1	1 AWG	3 AWG	1	TAN	CD9	KA12-1/0
PT1	1 AWG	-	-	3 AWG	1	-	BG 52	-
-	-	PTS1/0	1/0 AWG	2 AWG	2	TAN	CD9	KA12-1/0
PT1/0	1/0 AWG	-	-	2 AWG	2	RED	CD16A	KC12-350
-	-	PTS2/0 PTO2/0	2/0 AWG	1 AWG	2	WHITE	CD15A	KA12-4/0
PT2/0	2/0 AWG	-	-	1 AWG	2	RED	CD16A	KC12-350
-	-	PTS3/0 PTO3/0	3/0 AWG	1/0 AWG	2	WHITE	CD15A	KA12-4/0
PT3/0	3/0 AWG	-	-	1/0 AWG	2	RED	CD16A	KC12-350
-	-	PTS4/0 PTO4/0	4/0 AWG	2/0 AWG	2	WHITE	CD15A	KA12-4/0
PT4/0	4/0 AWG	-	-	2/0 AWG	2	RED	CD16A	KC12-350
-	-	PTS250 PTO250	250 MCM	3/0 AWG	2	BROWN	CD18A	KA12-350
PT250	250 MCM	-	-	3/0 AWG	2	BROWN	CD18A	KA12-350
-	-	PTS300 PTO300	300 MCM	4/0 AWG	2	BROWN	CD18A	KA12-350
PT300	300 MCM	-	-	4/0 AWG	2	BROWN	CD18A	KA12-350
-	-	PTS350 PTO350	350 MCM	250 MCM	2	BROWN	CD18A	KA12-350
PT350	350 MCM	-	-	4/0 AWG	2	BROWN	CD18A	KA12-350
-	-	PTS400 PTO400	400 MCM	300 MCM	2	PINK	CD20	KA12-500
PT400	400 MCM	-	-	250 MCM	2	PINK	CD20	KA12-500
-	-	PTS500 PTO500	500 MCM	350 MCM	2	PINK	CD20	KA12-500
PT500	500 MCM	-	-	350 MCM	2	PINK	CD20	KA12-500
-	-	PTS600 PTO600	600 MCM	400 MCM	2	YELLOW	CD23	-
PT600	600 MCM	-	-	350 MCM	2	YELLOW	CD23	-
-	-	PTS750 PTO750	750 MCM	500 MCM	2	YELLOW	CD23	-
PT750	750 MCM	-	-	500 MCM	2	YELLOW	CD23	-
-	-	-	-	-	-	LISTED TOOLS	N1240 NSI-12 P-750	HK1240

* REQUIRES 15 TON TOOL

TOOL AND DIE CHARTS