

AUDIOVISUAL

| ANSI Code | Product Number | Ordering Abbreviation | Application | Watts | Volts | Base | Lumens | Avg Rated Life(hrs) | Bulb | Pkg Qty | Footnotes |
|-----------|----------------|-----------------------|--|-------|-------|--------|--------|---------------------|-------|---------|-----------|
| EPX | 54927 | EPX | Projector - Microfilm | 90 | 14 | GX5.3 | 43 | 500 | MR16 | 24 | 4 |
| EPZ | 54743 | EPZ | Projector - Microfilm | 50 | 14 | GX5.3 | 80 | 3000 | MR16 | 24 | 4 |
| ERK | 55050 | ERK BULK | Projector | 12 | 6 | Wedge | | 150 | T2.25 | 500 | |
| ERM | 55054 | ERM BULK | Projector | 7 | 6 | Wedge | | 30 | T2.25 | 500 | |
| ESA/FHD | 54025 | ESA/FHD 64225 | Projector | 10 | 6 | G4 | 200 | 100 | T3 | 100 | |
| ESB | 54019 | ESB 64250 HLX | Projector | 20 | 6 | G4 | 480 | 100 | T3.5 | 100 | |
| ETJ | 54928 | ETJ | Projector | 250 | 120 | GY5.3 | 600 | 175 | MR16 | 24 | 4 |
| EVA | 54052 | EVA 64623 HLX | Projector, Microfilm, Microscope, Studio | 100 | 12 | GY6.35 | 2800 | 2000 | T4 | 100 | |
| EVC | 54047 | EVC 64657 HLX | Projector, Microfilm, Microscope, Studio | 250 | 24 | G6.35 | 9000 | 300 | T4 | 100 | |
| EVD | 54100 | EVD 64663 HLX | Projector, Microfilm, Studio | 400 | 36 | G6.35 | 16000 | 50 | T6 | 24 | 6 |
| EVD | 54103 | EVD 64663 HLX BULK | Projector, Microfilm, Studio | 400 | 36 | G6.35 | 16000 | 50 | T6 | 100 | |
| EVW | 54723 | EVW | Projector | 250 | 82 | GY5.3 | 390 | 50 | MR16 | 24 | 4 |
| EXR | 54392 | EXR | Projector - Slide | 300 | 82 | GX5.3 | 925 | 35 | MR13 | 24 | 4 |
| EXR | 54393 | EXR BULK | Projector - Slide | 300 | 82 | GX5.3 | | 35 | MR13 | 100 | 4 |
| EXW | 54388 | EXW | Projector - Slide | 300 | 82 | GX5.3 | 1050 | 15 | MR13 | 24 | 4 |
| EXY | 54394 | EXY | Projector - Slide | 250 | 82 | GX5.3 | 400 | 200 | MR13 | 24 | 4 |
| EYB | 54446 | EYB | Projector, Stage & Studio | 360 | 82 | G5.3 | 10000 | 75 | T3.5 | 24 | |
| EYB-5 | 54448 | EYB-5 | Projector, Microfilm, Stage & Studio | 360 | 86 | G5.3 | 10000 | 75 | T3.5 | 24 | |
| EYB-7 | 54455 | EYB-7 | Projector, Microfilm, Stage & Studio | 360 | 88 | G5.3 | 10000 | 75 | T3.5 | 24 | |
| EZE | 54386 | EZE | Projector, Stage & Studio | 150 | 82 | GX5.3 | 350 | 150 | MR13 | 24 | 4 |
| FBV | 54568 | FBV | Projector, Microfilm, Stage & Studio | 250 | 30 | E10 | 7000 | 6 | T3 | 12 | |
| FCR | 54036 | FCR 64625 HLX | Projector, Microfilm, Microscope, Studio | 100 | 12 | GY6.35 | 3600 | 50 | T3.5 | 100 | |
| FCS | 54041 | FCS 64640 HLX | Projector | 150 | 24 | G6.35 | 6000 | 50 | T4 | 100 | |
| FCS | 54042 | FCS 64640 HLX BULK | Projector | 150 | 24 | G6.35 | 6000 | 50 | T4 | 250 | |
| FDS/DZE | 54055 | FDS/DZE 64643 | Projector, Microfilm, Microscope, Studio | 150 | 24 | GY9.5 | 5000 | 100 | T4 | 30 | |
| FDT 64628 | 54031 | FDT 64628 | Projector, Stage & Studio | 100 | 12 | GY9.5 | 3000 | 50 | T4 | 30 | |
| FDV | 54054 | FDV 64642 HLX | Projector, Microfilm, Microscope, Studio | 150 | 24 | G6.35 | 5000 | 300 | T4 | 100 | |
| FHS | 54979 | FHS | Projector - Slide | 300 | 82 | GX5.3 | 650 | 70 | MR16 | 24 | 4 |
| FKT/EYH | 54547 | FKT/EYH | Projector - Video Camera | 250 | 120 | G5.3 | 5400 | 200 | T6 | 24 | |
| FLE | 54383 | FLE | Projector | 360 | 82 | GY5.3 | 1250 | 75 | MR16 | 24 | 4,7 |
| FLT | 54440 | FLT | Projector - Video Camera, Microfilm | 25 | 14 | G4 | | 500 | MR11 | 24 | 8 |
| FNS | 58635 | FNS 64512 | Projector, Stage & Studio | 300 | 120 | GX6.35 | 9500 | 15 | T5 | 25 | |
| FNT | 54044 | FNT 64656PT HLX | Projector, Microfilm, Microscope, Studio | 275 | 24 | G6.35 | 10000 | 75 | T4 | 100 | |