

**DISCHARGE****HMI® METAL HALIDE***HMI® SINGLE END*

Ordering Abbreviation	Product Number	Watts (W)	Volts (V)	Current (A)	CRI	Lumens (lm)	Color Temp
HMI 200W/SE	54220	200	70	3.0	90	16000	6000
HMI 250W/SE	54062	270	50	5.0	90	16200	6000
HMI 400 W/SE	54219	400	70	6.9	90	33000	6000
HMI 575W/SEL/XS	54063	575	95	7.0	90	49000	6000
HMI 1200W/SEL/XS	54067	1200	100	13.8	90	110000	6000
HMI 1800W/SE/XS	54177	1800	123	14.6	90	165000	6000
HMI 2500W/SE/XS	54070	2500	115	25.6	90	240000	6000
HMI 4000W/SE/XS	54321	4000	200	24.0	90	380000	6000
HMI 6000W/SE/XS	54099	6000	123	55	90	600000	6000
HMI 12000W/SE/XS	54113	12000	160	84	90	1150000	6000
HMI 18000W/SE GX51	54324	18000	225	88	90	1600000	6000

*HMI® DOUBLE END*

Ordering Abbreviation	Product Number	Watts (W)	Volts (V)	Current (A)	CRI	Lumens (lm)	Color Temp
HMI 575 W/DXS	54313	575	95	7.0	90	49000	6000
HMI 1200 W/DXS	55139	1200	100	13.8	90	110000	6000
HMI 2500 W/DXS	54265	2500	115	25.6	90	240000	6000
HMI 2500W/S/XS	54068	2500	115	25.6	90	240000	6000
HMI 4000 W/DXS	54314	4000	200	24.0	90	380000	6000
HMI 6000 W/DXS	54315	6000	123	55.0	90	570000	6000
HMI 12000 W/DXS	54316	12000	240	84.0	90	1150000	6000
HMI 18000W/DXS	54213	18000	232	78	90	1700000	6000
HMI 24000W/DXS	54325	24000	280	86	90	2300000	6000

**HSD® 4ARXS METAL HALIDE**

Ordering Abbreviation	Product Number	Watts (W)	Volts (V)	Current (A)	CRI	Lumens (lm)	Color Temp
HSD 150W/70 4ARXS	54311	150	92	1.8	85	12000	7000
HSD 150W/UL/75 4ARXS	54312	150	98	1.8	85	11000	7500
HSD 200W/60 4ARXS	54167	200	65	3.3	80	13000	6000
HSD 250W/60 4ARXS	54170	250	85	3.1	85	17000	6000
HSD 250W/80 4ARXS	54243	250	85	3.2	85	17000	8000
HSD 250W/UL/75 4ARXS	54288	250	85	3.1	85	15000	7500
HSD 575W/72 4ARXS	54129	575	80	7.4	85	45000	7200

For the current listing of available products and more complete product information, please visit us at [www.sylvania.com](http://www.sylvania.com)