

Incandescent 20-51

Halogen 52-70

Compact Fluorescent 71-86

Fluorescent 87-120

## SPECIALTY LAMPS

Product Number	Ordering Code	Watts	Description	Nom. Length (in.)	Bulb	Base	Rated Avg. Life (hrs.) <sup>1)</sup>	UVA Watts
<b>UVA 365NM PEAK LAMPS<sup>1)</sup></b>								
15752-9	PL-S 9W/08 (Lead Free)	9	UVA Lamp	6½	PL-S	G23	3000	
15766-9	PL-S 9W/10 (Lead Free)	9	UVA Lamp	6½	PL-S	G23	2000	1.9
15765-1	PL-S 9W/10ZP	9	UVA Lamp	6½	PL-S	G23	9000	
13036-9	F15T8/BL	15	Black Light	18	T8	Med Bipin	5000	3.1
13034-4	PL-L 18W/10	18	UVA Lamp	9	PL-L	2G11	5000	3.4
19523-9	PL-L 36W/01/4P	36	UVA Lamp	16½	PL-L	2G11	5000	
39152-4	F20T12/BL	20	Black Light	24	T12	Med Bipin	5000	3.7
39153-2	F40T12/BL	40	Black Light	48	T12	Med Bipin	9000	9
15808-9	TL 40W/01	40	UVA Lamp	48	T12	Med Bipin	3000	
24675-1	TLK 40W/1QR	40	UVA Reflector Lamp	24	T12	Med Bipin	3000	7.4
26169-3	TL 60W/1QR	60	UVA Reflector Lamp	48	T12	Med Bipin	1000	15.8
26885-4	TL 80W/1QR	80	UVA Reflector Lamp	60	T12	Med Bipin	1000	20.5
24694-2	TL 100W/1QR	100	UVA Reflector Lamp	70	T12	Med Bipin	1000	26.6
24696-7	TL 140W/1QR	140	UVA Reflector Lamp	60	T12	Med Bipin	1000	37
24697-5	TL 176D38/10	140	UVA Lamp	70	T12	Med Bipin	1000	38.2
24698-3	TL 176D38/1QR	140	UVA Reflector Lamp	70	T12	Med Bipin	1000	31.7
†21513-7	Actinic BL 8W/10 250PK	8	UVA Lamp	20	T5	Min. Bipin	3000	
†21518-6	Actinic BL 15W/10 Secura 25PK	15	UVA Lamp	18	T8	Med Bipin	3000	
†21520-2	Actinic BL 20W/10 Secura 25PK	20	UVA Lamp	24	T12	Med Bipin	3000	
†21517-8	Actinic BL 30W/10 25PK	30	UVA Lamp	24	T8	Med Bipin	2000	
†21514-5	Actinic BL TL-K 40W/10 25PK	40	UVA Lamp	24	T12	Med Bipin	2000	
†21519-4	Actinic BL TL-K 40W/10 Secura 25PK	40	UVA Lamp	24	T12	Med Bipin	2000	

<sup>1)</sup> Based average life is the length of operation (in hours) at which point 50% of a large sample of lamps will still be operational and 50% will not.

†) For graphic arts, laser curing and insect trap applications.

† — New product.

For the most current product information go to the e-catalog on [www.philips.com](http://www.philips.com)



170 Philips Lighting Company SAG100 2008-2009