

Incandescent 20-51

Halogen 52-70

Compact Fluorescent 71-86

Fluorescent 87-120

## INCANDESCENT LAMPS

### Natural Light

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Qty	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.) <sup>(9)</sup>	Approx. MBCP <sup>+</sup>	Lumens
<b>NATURAL LIGHT STANDARD</b>														
40	A19	Med.	13558-2	▲	40A/NTL 12/4	120	48	Natural Light Standard	C, CC-6	4 1/4	1000	1000		400
60	A19	Med.	13559-0	▲	60A/NTL 12/4	120	48	Natural Light Standard	C, CC-6	4 1/4	1000	1000		680
75	A19	Med.	13560-8	▲	75A/NTL 12/4	120	48	Natural Light Standard	C, CC-6	4 1/4	750	750		950
100	A19	Med.	13561-6	▲	100A/NTL 12/4	120	48	Natural Light Standard	C, CC-6	4 1/4	750	750		1350
<b>NATURAL LIGHT STANDARD LONG LIFE</b>														
75	A19	Med.	15129-0		75A/NTL/2X 12/4	120	48	Natural Light Standard Long Life	C, CC-6	4 1/4	1500	1500		790
100	A19	Med.	15130-8		100A/NTL/2X 12/4	120	48	Natural Light Standard Long Life	C, CC-6	4 1/4	1500	1500		1210
<b>NATURAL LIGHT 3-WAY</b>														
50 100 150	A21	3 Ct. Med.	13564-0	▲ (8)	50/150A/NTL 12/1	120	12	Natural Light 3-Way	C, 2CC-6	5 1/4	1200			490 1250 1740
<b>NATURAL LIGHT GLOBE</b>														
40	G25	Med.	13563-3	▲	40G25/NTL 6/1	120	6	Natural Light Globe	C, CC-6	4 1/4	1500	1500		320
60	G25	Med.	13562-4	▲	60G25/NTL 6/1	120	6	Natural Light Globe	C, CC-6	4 1/4	1500	1500		560
<b>NATURAL LIGHT FAN</b>														
40	A15	Med.	13565-7	▲	BC40A15FAN/NTL 6/2	120	12	Natural Light Fan	C, C-9	3 1/2	1500	1500		340
<b>NATURAL LIGHT REFLECTOR</b>														
50	R20	Med.	13797-5	▲ (87)	50R20/FL/NTL 12/1	120	12	Natural Light Reflector	C, CC-6	3 1/4	2000	2000		265
65	BR30	Med.	13785-1	▲ (87)	65BR30/FL/NTL 12/1	120	12	Natural Light Reflector	C, CC-6	5 1/4	2000	2000		500
<b>NATURAL LIGHT DECORATIVE</b>														
40	G16 1/2	Cand.	14129-1	▲ (12)	BC40G16-1/2/NTL 6/2	120	12	Natural Light Decorative	C, CC-2V, C-7A	3	2000	2000		270
	B10 1/2	Cand.	14125-9	▲ (12)	BC40B10-1/2/NTL 6/2	120	12	Natural Light Decorative	C, CC-2V, C-7A	4 1/4	2000	2000		270
	B13	Med.	14127-5	▲ (12)	BC40B13/NTL 6/2	120	12	Natural Light Decorative	C, C-7A, CC-2V	4 1/4	2000	2000		270
60	G16 1/2	Cand.	14130-9	▲ (12)	BC60G16-1/2/NTL 6/2	120	12	Natural Light Decorative	C, C-7A, CC-2V	3	2000	2000		510
	B10 1/2	Cand.	14126-7	▲ (12)	BC60B10-1/2/NTL 6/2	120	12	Natural Light Decorative	C, C-7A, CC-2V	4 1/4	2000	2000		510
	B13	Med.	14128-3	▲ (12)	BC60B13/NTL 6/2	120	12	Natural Light Decorative	C, C-7A, CC-2V	4 1/4	2000	2000		510

For the most current product information, go to the e-catalog on [www.philips.com](http://www.philips.com)  
Incandescent symbols and footnotes located on page 51



28 Philips Lighting Company SAGI 00 2008-2009