

# PAR30L

75W 120V PAR30L SP 16D 1CT



Philips Halogen PAR lamps will provide bright, white light across the product line and feature excellent beam qualities for accent or ambient lighting. Their optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering, making it easy to optimize the look and feel of your store and your merchandise.

## Product data

### • General Characteristics

|                                |                                      |
|--------------------------------|--------------------------------------|
| Base                           | Medium [Single Contact Medium Screw] |
| Base Information               | Brass [Brass Base]                   |
| Bulb                           | PAR30L [PAR 3.75 inch/95mm Long]     |
| Bulb Material                  | Hard Glass                           |
| Bulb Finish                    | Clear                                |
| Reflector Finish               | Aluminized                           |
| Filament Shape                 | CC-8 [Axial]                         |
| Operating Position             | Universal [Any or Universal (U)]     |
| Main Application               | Accent & Downlighting                |
| Atmosphere                     | Gas                                  |
| RatedAvgLife(See Family Notes) | 2000 hr                              |
| Estimated Energy Cost/YR       | 9.03 \$                              |
| Life with 3h/day use [years]   | 1.8 an                               |

### • Light Technical Characteristics

|                       |         |
|-----------------------|---------|
| Beam Description      | Spot    |
| Beam Angle            | 16 D    |
| Approx. MBCP          | 6700 cd |
| Color Rendering Index | 100 Ra8 |

|                   |        |
|-------------------|--------|
| Color Temperature | 2860 K |
| Initial lumen     | 975 Lm |

### • Electrical Characteristics

|         |       |
|---------|-------|
| Watts   | 75 W  |
| Voltage | 120 V |


### • Product Dimensions

|            |         |
|------------|---------|
| Diameter D | 3.75 in |
|------------|---------|


### • Product Data

|                    |                            |
|--------------------|----------------------------|
| Product number     | 229344                     |
| Full product name  | 75W 120V PAR30L SP 16D 1CT |
| Short product name | 75W 120V PAR30L SP 16D 1CT |
| Pieces per Sku     | 1                          |
| eop_pck_cfg        | 15                         |
| Skus/Case          | 15                         |
| Bar code on pack   | 46677229344                |
| Bar code on case   | 50046677229349             |
| Logistics code(s)  | 924757140301               |
| eop_net_weight_pp  | 0.001 kg                   |

Dimensional drawing



E26, PAR30L



E26, PAR30L



E26



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change