

### Group AA

VA	Catalog Number	Fig.	Dim. (A)	Dim. (B)	Dim. (C)	Dim. (D)	Dim (E)	Wiring Diagram	Est. Ship Wgt. (lbs)
<b>220/230/240 x 440/460/480 - 110/115/120</b>									
50	631-1101-300	30	3.64	3.00	3.46	2.00	2.50	Group AA	2.60
75	631-1201-300	30	4.10	3.00	3.46	2.50	2.50		3.50
100	631-1301-300	30	4.10	3.31	3.46	2.38	2.81		4.20
150	631-1401-300	30	4.54	3.75	3.94	2.88	3.13		6.70
200	631-1501-300	30	4.37	4.50	4.46	2.50	3.75		8.50
250	631-1601-300	30	4.87	4.50	4.47	2.88	3.75		10.00
300	631-1701-300	30	4.87	4.50	4.47	3.25	3.75		11.30
350	631-1801-300	30	5.60	4.50	4.47	3.75	3.75		13.60
500	631-1901-300	31	5.53	5.25	5.66	3.88	4.38		19.20
750	631-2001-300	31	6.77	5.25	5.66	5.38	4.38		28.10
1000	631-2101-300	31	6.02	6.37	6.57	4.00	6.13		28.10
1500	631-2201-300	31	7.03	6.37	6.57	4.50	6.13		30.00
2000	631-2301-300	31	7.79	6.37	6.57	5.13	6.13		38.00
3000	631-2401-301	31	7.01	9.00	8.74	4.25	6.50		53.00
5000	631-2601-301	31	8.00	9.00	8.74	7.25	7.50		89.00

### Group BB

VA	Catalog Number	Fig.	Dim. (A)	Dim. (B)	Dim. (C)	Dim. (D)	Dim (E)	Wiring Diagram	Est. Ship Wgt. (lbs)
<b>240x480 - 24</b>									
50	631-1102-300	30	3.64	3.00	3.46	2.00	2.50	Group BB	2.60
75	631-1202-300	30	4.10	3.00	3.46	2.50	2.50		3.50
100	631-1302-300	30	4.10	3.31	3.46	2.38	2.81		4.20
150	631-1402-300	30	4.54	3.75	3.94	2.88	3.13		6.70
200	631-1502-300	30	4.37	4.50	4.46	2.50	3.75		8.50
250	631-1602-300	30	4.87	4.50	4.47	2.88	3.75		10.00
300	631-1702-300	30	4.87	4.50	4.47	3.25	3.75		11.30
350	631-1802-300	30	5.60	4.50	4.47	3.75	3.75		13.60
500	631-1902-300	31	5.53	5.25	5.66	3.88	4.38		19.20
750	631-2002-301	31	6.77	5.25	5.66	5.38	4.38		28.10

