

Incandescent 20-51

Halogen 52-70

Compact Fluorescent 71-86

Fluorescent 87-120

HALOGEN LAMPS

Halogená® Lamps

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.	Description	Class, Filament	MCL (In.)	Rated Avg. Life (Hrs.) ⁽⁹³⁾	Approx. MB ^{CP} *	Lumens
HALOGENÁ® ENERGY SAVER													
40	T60	Med.	20967-6	\$ @ □ † (103)	40T60/HES/WH	120	6	White	C, CC-8	4 1/4	3000	—	800
	R20	Med.	21202-7	\$ @ □ † (104)	40R20/HES/FL	120	6	Flood	C, CC-8	3 3/4	3000	—	570
	BR30	Med.	20970-0	\$ @ □ † (104)	40BR30/HES/FL	120	5	Flood	C, CC-8	5 1/4	3000	—	600
	BR40	Med.	20972-6	\$ @ □ † (104)	40BR40/HES/FL	120	4	Flood	C, CC-8	6 1/4	3000	—	630
70	T60	Med.	20969-2	\$ @ □ † (103)	70T60/HES/WH	120	6	White	C, CC-8	4 1/4	3000	—	1600
HALOGENÁ® ENERGY ADVANTAGE PRO PACKS (102)													
40	T60	Med.	21354-6	\$ @ □ † (103)	40T60/HEA/WH	120	12	White	C, CC-8	4 1/4	3000	—	800
	R20	Med.	22236-4	\$ @ □ † (104)	40R20/HEA/FL	120	12	Flood	C, CC-8	3 3/4	3000	450	—
	BR30	Med.	21359-5	\$ @ □ † (104)	40BR30/HEA/FL	120	12	Flood	C, CC-8	5 1/4	3000	2250	—
50	T60	Med.	21356-1	\$ @ □ † (103)	50T60/HEA/WH	120	12	White	C, CC-8	4 1/4	3000	—	1100
70	T60	Med.	21358-7	\$ @ □ † (103)	70T60/HEA/WH	120	12	White	C, CC-8	4 1/4	3000	—	1600
HALOGENÁ® CLASSIC BLISTER-CARDED (96)													
60	BT 15	Med.	24924-3		BC 60BT15/HAL/CL	120	10	Clear Blister Card	C, CC-8	4	3000	—	900
			24926-8		BC 60BT15/HAL/W	120	10	White Blister Card	C, CC-8	4	3000	—	840
			38915-5		BC 60BT15/HAL/W	120	80	White Blister Card	C, CC-8	4	3000	—	840
75	BT 15	Med.	24927-6		BC 75BT15/HAL/W	120	10	White Blister Card	C, CC-8	4	3000	—	1120
100	BT 15	Med.	24931-8		BC 100BT15/HAL/W	120	10	White Blister Card	C, CC-8	4	3000	—	1670
150	BT 15	Med.	24933-4		BC 150BT15/HAL/W	120	10	White Blister Card	C, CC-8	4	3000	—	2650
HALOGENÁ® CLASSIC BLISTER-CARDED—REDUCED WATTAGE (96, 102)													
55	BT 15	Med.	21378-5	\$ (101)	BC 55BT15/HAL/CL	120	10	Clear Blister Card	C, CC-8	4	3000	—	825
			21280-1	\$	BC 55BT15/HAL/CL	120	4	Clear Blister Card	C, CC-8	4	3000	—	825
			21379-3	\$ (101)	BC 55BT15/HAL/W	120	10	White Blister Card	C, CC-8	4	3000	—	770
			21381-9	\$	BC 55BT15/HAL/W	120	4	White Blister Card	C, CC-8	4	3000	—	770
CP19	Med.	21383-5	\$ □	BC 55CP19/HAL/CL	120	6	Clear Blister Card	C, CC-8	4 1/4	3000	—	825	
70	BT 15	Med.	21386-8	\$ (101)	BC 70BT15/HAL/W	120	10	White Blister Card	C, CC-8	4	3000	—	1045
			21387-6	\$	BC 70BT15/HAL/W	120	4	White Blister Card	C, CC-8	4	3000	—	1045
95	BT 15	Med.	21391-8	\$ (101)	BC 95BT15/HAL/W	120	10	White Blister Card	C, CC-8	4	3000	—	1500
			21392-6	\$	BC 95BT15/HAL/W	120	4	White Blister Card	C, CC-8	4	3000	—	1500

For the most current product information go to the e-catalog on www.philips.com
Halogen symbols and footnotes located on page 70



56 Philips Lighting Company SAGI 00 2008-2009