



PL-C Cluster 2-Pin Base

PL-C ALTO 26W/830/2P 1CT

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

• General Characteristics

Base	G24d-3
Base Information	2P
Avg. Life	10000 hr
Life to 10% failures EM	6500 hr
LSF EM 8000h Rated, 3h cycle	78 %
LSF EM 6000h Rated, 3h cycle	92 %
LSF EM 4000h Rated, 3h cycle	98 %
LSF EM 2000h Rated, 3h cycle	99 %

• Light Technical Characteristics

Color Code	830 [CCT of 3000K]
Color Rendering Index	82 Ra8
Color Designation	Warm White
Color Temperature	3000 K
Chromaticity Coordinate X	435 -
Chromaticity Coordinate Y	400 -
Lum Efficacy Rated EM 25°C	68 Lm/W
LLMF EM 8000h Rated	81 %
LLMF EM 6000h Rated	84 %
LLMF EM 4000h Rated	87 %
LLMF EM 2000h Rated	92 %

Luminous Flux EM 25°C, Rated	1800 Lm
Luminous Flux EM 25°C, Nominal	1800 Lm
Design Temperature	28 C

• Electrical Characteristics

Watts	26 W
Dimmable	No
Lamp Current EM 25°C	0.325 A
Lamp Wattage EM 25°C, Rated	26.5 W
Lamp Wattage EM 25°C, Nominal	26 W
Lamp Voltage EM 25°C	100 V

• Environmental Characteristics

Energy Efficiency Label (EEL)	B
Mercury (Hg) Content	1.4 mg

• Product Dimensions

Base Face to Base Face A	130.7 (max) mm
Insertion Length B	149.0 (max) mm
Overall Length C	171.4 (max) mm
Diameter D	27.1 (max) mm
Diameter D1	27.1 (max) mm

PHILIPS

sense and simplicity



PL-C Cluster 2-Pin Base

Product Data

Product number 383224
 Full product name PL-C ALTO 26W/830/2P 1CT
 Short product name PL-C 26W/30 ALTO 10PK
 Pieces per Sku 1
 eop_pck_cfg 10

Skus/Case 10
 Bar code on pack 46677114947
 Bar code on case 60046677114949
 Logistics code(s) 927913883020
 tpd_ilcos_cd FSQ-26/30/1B-I-G24d=3
 eop_net_weight_pp 64.300 gr

Dimensional drawing





G24d-3

G24d-1/G24d-2/G24d-3, 2P

Product	A (Max)	B (Max)	C (Max)	D (Max)	D1 (Max)
PL-C ALTO 26W/830/2P	130.7	149.0	171.4	27.1	27.1

Photometric data



© 2012 Koninklijke Philips Electronics N.V.
 All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
 data subject to change