

# Support Products

## Pipe Straps

Plasti-Bond PVC coated pipe straps are used to securely mount conduit to a wall or other structure for support. They are available in two styles: a one-hole malleable iron strap or a two-hole stamped steel strap. Mounting hardware not provided.

### Features:

- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



### CONDUIT PIPE STRAP 1 HOLE

| PIPE SIZE | FERROUS CATALOG # | NOMINAL WT. FOR 100 |
|-----------|-------------------|---------------------|
| 1/2"      | PBPS11M           | 11                  |
| 3/4"      | PBPS22M           | 14                  |
| 1"        | PBPS33M           | 12                  |
| 1-1/4"    | PBPS44M           | 25                  |
| 1-1/2"    | PBPS55M           | 36                  |
| 2"        | PBPS66M           | 71                  |
| 2-1/2"    | PBPS77M           | 111                 |
| 3"        | PBPS88M           | 134                 |
| 3-1/2"    | PBPS99M           | 166                 |
| 4"        | PBPS100M          | 256                 |

### CONDUIT PIPE STRAP 2 HOLE

| PIPE SIZE | FERROUS CATALOG # | NOMINAL WT. FOR 100 |
|-----------|-------------------|---------------------|
| 1/2"      | PBPS11S-2         | 2.0                 |
| 3/4"      | PBPS22S-2         | 3.0                 |
| 1"        | PBPS33S-2         | 4.0                 |
| 1-1/4"    | PBPS44S-2         | 4.5                 |
| 1-1/2"    | PBPS55S-2         | 5.0                 |
| 2"        | PBPS66S-2         | 10.0                |
| 2-1/2"    | PBPS77S-2         | 13.0                |
| 3"        | PBPS88S-2         | 17.0                |
| 3-1/2"    | PBPS99S-2         | 20.0                |
| 4"        | PBPS100S-2        | 25.0                |

## Clamp Back Spacers

Plasti-Bond PVC coated clamp back spacers are used with malleable or stamped pipe straps to provide a mounting stand-off for a conduit from a wall or other structure.

### Features:

- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



### CONDUIT CLAMP BACK SPACER

| PIPE SIZE | FERROUS CATALOG # | NOMINAL WT. EACH |
|-----------|-------------------|------------------|
| 1/2"      | PBCLB-M50         | 0.1              |
| 3/4"      | PBCLB-M75         | 0.1              |
| 1"        | PBCLB-M100        | 0.1              |
| 1-1/4"    | PBCLB-M125        | 0.2              |
| 1-1/2"    | PBCLB-M150        | 0.2              |
| 2"        | PBCLB-M200        | 0.3              |
| 2-1/2"    | PBCLB-M250        | 1.0              |
| 3"        | PBCLB-M300        | 1.7              |
| 4"        | PBCLB-M400        | 2.0              |

## Conduit Clamp Hangers

Plasti-Bond PVC coated conduit clamp hangers are used with threaded rod to securely suspend conduit runs supported from above. They are provided with stainless steel hardware.

### Features:

- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



### CONDUIT HANGER

| PIPE SIZE | CATALOG # | NOMINAL WEIGHT |
|-----------|-----------|----------------|
| 1/2"      | PB6H0B    | 0.1            |
| 3/4"      | PB6H1B    | 0.1            |
| 1"        | PB6H2B    | 0.1            |
| 1-1/4"    | PB6H3B    | 0.1            |
| 1-1/2"    | PB6H4B    | 0.2            |
| 2"        | PB6H5B    | 0.3            |
| 2-1/2"    | PB6H6B    | 0.4            |
| 3"        | PB6H7B    | 0.5            |
| 3-1/2"    | PB6H8B    | 0.6            |
| 4"        | PB6H9B    | 0.7            |

## Thread Rods

Plasti-Bond PVC coated all thread rod is used with coated conduit hangers and coated strut to securely suspend conduit runs supported from above. It is provided in 3/8" and 1/2" sizes and three standard lengths, 3', 6' and 10'.

### Features:

- 20 mil gray PVC exterior coating
- 2 trade sizes and 3 standard lengths



### THREAD RODS

| SIZE       | CATALOG #     |
|------------|---------------|
| 3/8" X 3'  | PBH193-3/8X3  |
| 3/8" X 6'  | PBH193-3/8X6  |
| 3/8" X 10' | PBH193-3/8X10 |
| 1/2" X 3'  | PBH193-1/2X3  |
| 1/2" X 6'  | PBH193-1/2X6  |
| 1/2" X 10' | PBH193-1/2X10 |



Contact us:  
customerservice@plastibond.com



Visit [www.plastibond.com](http://www.plastibond.com)  
For more information