



PAR20

39PAR20/IRC+/FL30 120V 15/1

Philips Halogen PAR lamps will provide bright, white light across the product line and feature excellent beam qualities for accent or ambient lighting. Their optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering, making it easy to optimize the look and feel of your store and your merchandise.

Product data

• General Information

| | |
|------------------------------|-------------------------------|
| Cap-Base | Medium [Medium] |
| Bulb Shape | PAR20 [PAR 2.5 inch] |
| Operating Position | Universal [Universal] |
| Main Application | Track, Downlighting & Outdoor |
| Gas Filling | GAS |
| Life With 3 Hour Per Day Use | 4.0 a |

• Light Technical

| | |
|------------------------------------|----------------|
| Beam Angle (Nom) | 30 ° |
| Initial lumen (Nom) | 500 lm |
| Luminous Intensity (Nom) | 1090 cd |
| Beam Description | Flood [Flood] |
| Luminous Flux Lamp @ 120V | 500 lm |
| Correlated Color Temperature (Nom) | 2600 K |
| Color Rendering Index (Nom) | 100 |

• Operating and Electrical

| | |
|-------------------------|------|
| Power (Rated) (Nom) | 39 W |
| Lamp Wattage Rated@120V | 39 W |

| | |
|---------------|-------|
| Voltage (Nom) | 120 V |
|---------------|-------|

• Mechanical and Housing

| | |
|----------------------|----------------------------------|
| Bulb Finish | Clear (CL) |
| Cap-Base Information | Alum/Ni plated [Alum/Ni plated] |
| Bulb Material | Hard Glass |
| Reflector Finish | Aluminized |
| Filament Shape | CC-8 [Axial] |

• Approval and Application

| | |
|--|--------|
| Estimated Energy Cost Per Year At 120V | 4.7 \$ |
| Estimated Energy Cost Per Year | 4.7 \$ |

• Product Data

| | |
|---------------------------------|-----------------------------|
| Order product name | 39PAR20/IRC+/FL30 120V 15/1 |
| EAN/UPC - Product | 046677453787 |
| Order code | 453787 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 15 |
| Material Nr. (12NC) | 925720236301 |
| Net Weight (Piece) | 100.000 g |


PHILIPS

Dimensional drawing

PAR20 39W E26 120V FL 30D

Product

39PAR20/IRC+/FL30 120V 15/1



E26, PAR20, Narrow Spot



© 2015 Philips Lighting Holding B.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, November 29
data subject to change