

Plasti-Bond REDH₂O^T

Form 8 & Form 7 Conduit Bodies For General Service

Description:

Plasti-Bond conduit bodies with covers are offered in Form 8 and Form 7 styles, each with numerous configurations to provide a complete coated conduit system. May be used to make 90degree bends, for pull outlets, to provide for taps or splices, to act as a mounting outlet for wiring devices or lighting fixtures etc. Electrical continuity of the conduit system is maintained across assembled joints.

Features:

- 40 mil gray PVC exterior coating
- 2 mil red urethane internal coating
- 10 trade sizes from 1/2" through 4"
- Sealing sleeves on all conduit openings
- Form 7 style cover uses retained stainless screw and wedge clip design
- Form 8 style cover uses plastic encapsulated stainless steel screws with retainers built into covers for trade sizes 1/2" through 2".

Standards:

- UL Listed Standard 514B
- CSA Standard: C22.2 No. 18 Note: Form 7 fittings are not available with encapsulated screws. All cover screws are stainless steel. Form 8 fittings are shipped with encapsulated screws.



PRLB



PRT



PRL

Selected Product Numbers:
PRT37


Product Charts:

Use the check boxes to 'flag or note' your selections for quick reference. Click the Button "Update Selections" to reflect changes.

Plasti-Bond REDH₂OT[®]

<input type="checkbox"/>	PRX47	1-1/4"	9.94	4.17	2.35	1.75	5	3.6	-
<input type="checkbox"/>	PRX57	1-1/2"	11.19	4.67	2.6	1.94	5.44	5	-
<input type="checkbox"/>	PRX67	2"	13.19	5.23	3.17	2.44	6.38	7.5	-

T FORM 8



Edit Selection	Catalog Number	Size Inches	A	B	C	D	E	Weight	Aluminum Catalog Number
<input type="checkbox"/>	PRHT18	1/2"	6.69	1.79	2.2	1	3.31	1.8	PRT19
<input type="checkbox"/>	PRHT28	3/4"	7.78	2.04	2.35	1.19	3.94	2.5	PRT29
<input type="checkbox"/>	PRHT38	1"	9.31	2.29	2.67	1.38	4.56	3.3	PRT39
<input type="checkbox"/>	PRHT448	1-1/4"	11	2.67	3.2	1.75	5.31	4.9	PRT49
<input type="checkbox"/>	PRHT58	1-1/2"	13.38	2.82	4.04	2.13	6.5	7.5	PRT59
<input type="checkbox"/>	PRHT68	2"	16.25	3.6	5.04	3	8.56	11.7	PRT69
<input type="checkbox"/>	PRT78	2-1/2"	19.63	4.48	6.73	4.25	10.88	19.8	PRT789
<input type="checkbox"/>	PRT88	3"	19.63	4.85	6.73	4.25	10.88	23.5	PRT889
<input type="checkbox"/>	PRT989	3-1/2"	22.75	5.73	8.17	5.44	13.44	21	PRT989
<input type="checkbox"/>	PRT1089	4"	22.75	5.98	8.17	5.44	13.44	24	PRT1089

T FORM 7

Edit Selection	Catalog Number	Size Inches	A	B	C	D	E	Weight	Aluminum Catalog Number
<input type="checkbox"/>	PRT17	1/2"	6.63	1.79	2.48	0.94	3.19	1.5	PRT17SA
<input type="checkbox"/>	PRT27	3/4"	7.75	2.04	2.67	1.13	3.81	2.1	PRT27SA
<input checked="" type="checkbox"/>	PRT37	1"	9.25	2.29	3.04	1.38	4.5	2.9	PRT37SA
<input type="checkbox"/>	PRT47	1-1/4"	9.94	2.35	3.23	1.75	5	3.6	PRT47SA
<input type="checkbox"/>	PRT57	1-1/2"	11.19	2.6	3.6	1.94	5.44	4.5	PRT57SA
<input type="checkbox"/>	PRT67	2"	13.19	3.17	4.17	2.44	6.38	6.5	PRT67SA