

MasterColor CDM ED17 Protected Elite 4200K

MasterColor CDM 70W ED17P CO U ELITE/4K

MasterColor Elite Protected Ceramic Metal Halide ED-17 4200K
Lamps provide excellent lumen maintenance and outstanding performance over time in a protected lamp.



Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	ED17P [Protected]
Bulb Material	Hard Glass
Bulb Finish	Coated
Operating Position	Universal [Any or Universal (U)]
Main Application	General Lighting
RatedAvgLife(See Family Notes)	20000 hr

Lamp Voltage	100 V
Lamp Current	0.9 A
Ignition Time	10 (max) s
Re-ignition Time [min]	8 (max) min

• Environmental Characteristics

Mercury (Hg) Content	7.1 (max) mg
Picogram per Lumen Hour	79 p/LuHr

• Light Technical Characteristics

Color Code	940 [CCT of 4000K]
Color Rendering Index	87 (min), 90 (nom) Ra8
Color Designation	Cool White
Color Temperature	4000 K
Color Temperature technical	3900 K
Initial Lumens	5900 Lm
Luminous Efficacy Lamp	84 Lm/W
Lumen Maintenance - 10% life	90 %
Lumen Maintenance - 40% life	80 %
Design Mean Lumens	4720 Lm
Chromaticity Coordinate X	0.373 (min), 0.382 (nom), 0.391 (max)
Chromaticity Coordinate Y	0.357 (min), 0.363 (nom), 0.369 (max)

• UV-related Characteristics

Damage Factor D/fc	0.28 -
PET (NIOSH)	347 h500lx
UV A	9.2 mW/cm ²
UV B	0 mW/cm ²
UV C	0 mW/cm ²

• Luminaire Design Requirements

Cap-Base Temperature	190 (max) C
Bulb Temperature	400 (max) C

• Product Dimensions

Light Center Length L	3.44 in
Max Overall Length (MOL) - C	5.438 (max) in
Diameter D	2.125 in

• Electrical Characteristics

Watts	70 W
-------	------

PHILIPS

MasterColor CDM ED17 Protected Elite 4200K

Product Data

Product number 429976
 Full product name MasterColor CDM 70W ED17P CO U ELITE/4K
 Short product name MHC70/C/U/MP/4K ELITE
 Pieces per Sku 1


eop_pck_cfg 12
 Skus/Case 12
 Bar code on pack 46677429973
 Bar code on case 50046677429978
 Logistics code(s) 928601178001
 eop_net_weight_pp 0.001 kg

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will

remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Dimensional drawing



MasterColor CDM 70W ED17P CO U ELITE/4K

Product	C (Max)	D (Norm)
MHC P 70W/940 E26 ED17P CO U ELITE	5.438	2.125



E26



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, August 29
data subject to change