

PLASTI-BOND REDH₂O_T PLUGS AND BUSHINGS

PLUGS AND BUSHINGS

Bushings and Plugs Technical Data

RE = Reducers

RE style reducers reduce conduit hubs to a smaller size. They are provided with an integral bushing to prevent conductor damage and full, clean cut threads for ease of assembly. All RE reducers are coated inside and out with polyurethane for corrosion protection.

REDUCING BUSHINGS

Pipe Size	FERROUS Catalog #	Nominal Weight	Aluminum Catalog #
3/4" - 1/2"	PRRE21	0.2	PRRE21SA
1" - 1/2"	PRRE31	0.7	PRRE31SA
1" - 3/4"	PRRE32	0.5	PRRE32SA
1-1/4" - 1/2"	PRRE41	0.8	PRRE41SA
1-1/4" - 3/4"	PRRE42	0.8	PRRE42SA
1-1/4" - 1"	PRRE43	0.8	PRRE43SA
1-1/2" - 1/2"	PRRE51	0.9	PRRE51SA
1-1/2" - 3/4"	PRRE52	0.9	PRRE52SA
1-1/2" - 1"	PRRE53	0.9	PRRE53SA
1 1/2" - 1-1/4"	PRRE54	0.9	PRRE54SA
2" - 1/2"	PRRE61	1.1	PRRE61SA
2" - 3/4"	PRRE62	1.1	PRRE62SA
2" - 1"	PRRE63	1.2	PRRE63SA
2" - 1-1/4"	PRRE64	1.3	PRRE64SA
2" - 1-1/2"	PRRE65	1.6	PRRE65SA
2-1/2" - 1"	PRRE73	1.6	PRRE73SA
2 1/2" - 1-1/4"	PRRE74	1.6	PRRE74SA
2-1/2" - 1-1/2"	PRRE75	1.6	PRRE75SA
2-1/2" - 2"	PRRE76	1.7	PRRE76SA
3" - 1"	PRRE83	1.7	PRRE83SA
3" - 1-1/4"	PRRE84	2.3	PRRE84SA
3" - 1-1/2"	PRRE85	2.4	PRRE85SA
3" - 2"	PRRE86	2.5	PRRE86SA
3" - 2-1/2"	PRRE87	4.0	PRRE87SA
3-1/2" - 2"	PRRE96	4.6	PRRE96SA
3-1/2" - 2-1/2"	PRRE97	4.7	PRRE97SA
3-1/2" - 3"	PRRE98	4.8	PRRE98SA
4" - 2"	PRRE106	5.0	PRRE106SA
4" - 2-1/2"	PRRE107	5.2	PRRE107SA
4" - 3"	PRRE108	6.0	PRRE108SA
4" - 3-1/2"	PRRE109	6.1	PRRE109SA
5" - 4"	PRRE01210	7.4	PRRE01210SA
6" - 5"	PRRE01412	8.0	PRRE01412SA

GLL = Grounding Bushings

GLL style PVC coated threaded grounding bushings have an aluminum lug for copper or aluminum grounding conductors.

GROUNDING BUSHING

Pipe Size	FERROUS Catalog #	Nominal Weight
1/2"	PBGLL1	0.1
3/4"	PBGLL2	0.1
1"	PBGLL3	0.1
1-1/4"	PBGLL4	0.2
1-1/2"	PBGLL5	0.2
2"	PBGLL6	0.3
2-1/2"	PBGLL7	0.5
3"	PBGLL8	0.7
3-1/2"	PBGLL9	1.0
4"	PBGLL10	1.1

PLG = Plugs

PLG style plugs are used to close unused conduit hubs. They are available with either recessed square drive sockets or raised square drive heads. All PLG plugs are completely coated with polyurethane for corrosion protection.

SQUARE HEAD PLUGS

Pipe Size	FERROUS Catalog #	Nominal Weight
1/2"	PRPLG15	0.5
3/4"	PRPLG25	0.6
1"	PRPLG35	0.2
1-1/4"	PRPLG45	0.3
1-1/2"	PRPLG55	0.3
2"	PRPLG65	0.4
2-1/2"	PRPLG75	0.4
3"	PRPLG85	0.5
3-1/2"	PRPLG95	0.5
4"	PRPLG105	0.6

RECESSED PLUGS

Pipe Size	FERROUS Catalog #	Nominal Weight
1/2"	PRPLG1	0.2
3/4"	PRPLG2	0.2
1"	PRPLG3	0.3
1-1/4"	PRPLG4	0.3
1-1/2"	PRPLG5	0.3
2"	PRPLG6	0.3
2-1/2"	PRPLG7	0.3
3"	PRPLG8	0.4
3-1/2"	PRPLG9	0.4
4"	PRPLG10	0.5

APPROVAL STAMP