


SEE PAGE 9 FOR ACCESSORIES



15 & 20 Amp Straight Blade

AMPS	POLES/WIRES	VOLTAGE	NEMA CONFIG.	CONNECTOR	PLUG	SINGLE RECEPTACLE	DUPLEX RECEPTACLE	FLANGED INLET	FLANGED OUTLET	DUST RESISTANT INLET	DUST RESISTANT OUTLET
15	2P 3W	125	5-15R 5-15P	5269	5266	5251	5252	5278	5279	5278DRI	5279DRO
15	2P 3W	250	6-15R 6-15P	5669	5666	5651	5662	5678	5679	5678DRI	5679DRO
20	2P 3W	125	5-20R 5-20P	5369	5366	5351	5352	5378	5379	5378DRI	5379DRO
20	2P 3W	250	6-20R 6-20P	5469	5466	5461	5462	5478	5479	5478DRI	5479DRO


NEW!
NEW!

ConnectGlow™ Lighted Devices *See page 36 for more information.*

ConnectCharge™ Inlet System with Power Cord *See page 37 for more information.*

GFCI Duplex Receptacle

AMPS	POLES/WIRES	VOLTAGE	NEMA CONFIG.	DUPLEX RECEPTACLE
15	2P 3W	125	5-15R	1591-FI



Standard in Ivory.
Also available in Gray or White.

Part Numbers for Product Options (Min. order of 50) *White Body with Black Rear Housing is Standard*

Part No.	+	Housing Color*	+	Packaging	+	Option(s)
Part No.	+	<i>with white body only</i> YL (yellow) BU (blue) GY (gray) WH (white) RD (red) GN (green)	+	.OEM (50 pieces per pack)	+	.NI (no inserts)** .NE (no ears)** .CN (Robertson Head Screws)* <i>Note: Min. order of 10 for .CN option</i> .TM (no holes on DRO or DRI flanges; lock nut provided; available in TM.OEM pack only)

FOR ALL BLACK DEVICES
see page 30

*Example 1: 5266YL.OEM.NI Example 2: 205R.OEM.NE *Not available for receptacles. **Plugs and Connectors only. ***Receptacles only.*

Complete 15A Right-Angle Devices

AMPERAGE	POLES/WIRES	VOLTAGE	NEMA CONFIGURATION	CONNECTOR	PLUG
15	2P 3W	125	5-15R 5-15P	5269RA	5266RA




See pages 34 & 35 for right-angle devices and adapters



Ordering Options

- Individually boxed *or*
- Bulk packed 50 per carton with assembly screws backed-out.
Add suffix ".OEM" to the model number. Available only in black.



15RA Adapter *Compatible with the following devices*

AMPS	POLES/WIRES	VOLTAGE	NEMA CONFIG.	CONNECTOR	PLUG
15	2P 3W	125	5-15R 5-15P	5269	5266
15	2P 3W	250	6-15R 6-15P	5669	5666
20	2P 3W	125	5-20R 5-20P	5369	5366
20	2P 3W	250	6-20R 6-20P	5469	5466