


POLYSTAR™

| Part # | Size | Description |
|-------------------------------|-------------|--|
| OPAQUE COVER ENCLOSURE | | |
| PC806 | 8 x 6 x 4 | PolyStar™ Series Enclosure with Opaque Cover |
| PC1008 | 10 x 8 x 4 | PolyStar™ Series Enclosure with Opaque Cover |
| PC1210 | 12 x 10 x 6 | PolyStar™ Series Enclosure with Opaque Cover |
| PC1412 | 14 x 12 x 6 | PolyStar™ Series Enclosure with Opaque Cover |
| PC1614 | 16 x 14 x 8 | PolyStar™ Series Enclosure with Opaque Cover |
| CLEAR COVER ENCLOSURE | | |
| PC806CC | 8 x 6 x 4 | PolyStar™ Series Enclosure with Clear Cover |
| PC1008CC | 10 x 8 x 4 | PolyStar™ Series Enclosure with Clear Cover |
| PC1210CC | 12 x 10 x 6 | PolyStar™ Series Enclosure with Clear Cover |
| PC1412CC | 14 x 12 x 6 | PolyStar™ Series Enclosure with Clear Cover |
| PC1614CC | 16 x 14 x 8 | PolyStar™ Series Enclosure with Clear Cover |
| BACK PANELS | | |
| BP86AL | 8 x 6 | Aluminum Back Panel |
| BP108AL | 10 x 8 | Aluminum Back Panel |
| BP1210AL | 12 x 10 | Aluminum Back Panel |
| BP1412AL | 14 x 12 | Aluminum Back Panel |
| BP1614AL | 16 x 14 | Aluminum Back Panel |
| SWING PANEL KITS | | |
| PC806SPK | 8 x 6 | PolyStar™ Series 8x6 Swing Panel Kit (comes with mounts, screws and panel) |
| PC1008SPK | 10 x 8 | PolyStar™ Series 10x8 Swing Panel Kit (comes with mounts, screws and panel) |
| PC1210SPK | 12 x 10 | PolyStar™ Series 12x10 Swing Panel Kit (comes with mounts, screws and panel) |
| PC1412SPK | 14 x 12 | PolyStar™ Series 14x12 Swing Panel Kit (comes with mounts, screws and panel) |
| PC1614SPK | 16 x 14 | PolyStar™ Series 16x14 Swing Panel Kit (comes with mounts, screws and panel) |
| ACCESSORIES | | |
| PCSNK | | Slot Nut Kit (includes two nuts & two screws) |
| PCSPMK | | Swing Panel Mounts (4 per kit) |
| PCLATCHKIT | | Latch kit (2 latches per kit) - replacement only |
| PCACCESSORYKIT | | Accessory kit (includes all screws, inserts, and mounting feet) - replacement only |



Dimensions (inches)

| Enclosure | A x B | C | D | E | F | G | H | I | Back Panel | Sub-Panel |
|-------------|---------------|-------|-------|------|-----|------|-----|------|---------------|-----------------|
| 8 x 6 x 4 | 6.25 x 4.25 | 8.75 | 6.75 | 9.4 | 5.7 | 8.3 | 5 | 6.3 | 6.75 x 4.75 | 7.625 x 5.625 |
| 10 x 8 x 4 | 8.25 x 6.25 | 10.75 | 8.75 | 11.4 | 6.2 | 10.3 | 5.5 | 8.3 | 8.75 x 6.75 | 9.625 x 7.625 |
| 12 x 10 x 6 | 10.25 x 8.25 | 12.75 | 10.75 | 13.4 | 7.7 | 12.3 | 7 | 10.3 | 10.75 x 8.75 | 11.625 x 9.625 |
| 14 x 12 x 6 | 12.25 x 10.25 | 14.75 | 12.75 | 15.4 | 7.7 | 14.3 | 7 | 12.3 | 12.75 x 10.75 | 13.625 x 11.625 |
| 16 x 14 x 8 | 14.25 x 12.25 | 16.75 | 14.75 | 17.4 | 9.7 | 16.3 | 9 | 14.3 | 14.75 x 12.75 | 15.625 x 13.625 |