



# SPECIALTY BULBS

Line No.	Lamp No.	Bulb Type	Base	Des. Volts	Watts	MOL (Inch)	Fig. No.
1	3S6/5-120V-I	S-6	Candelabra Screw	120	3	1.88	91
2	3S6/5-130V-I	S-6	Candelabra Screw	130	3	1.88	91
3	3S6/5-140V-I	S-6	Candelabra Screw	140	3	1.88	91
4	3S6/5-145V-I	S-6	Candelabra Screw	145	3	1.88	91
5	3S6/5DC-120V-I	S-6	D.C. Bayonet	120	3	1.81	92
6	3S6/5DC-130V-I	S-6	D.C. Bayonet	130	3	1.81	92
7	6S6-6V-I	S-6	Candelabra Screw	6	6	1.88	91
8	6S6-12V-I	S-6	Candelabra Screw	12	6	1.88	91
9	6S6-18V-I	S-6	Candelabra Screw	18	6	1.88	91
10	6S6-24V-I	S-6	Candelabra Screw	24	6	1.88	91
11	6S6-30V-I	S-6	Candelabra Screw	30	6	1.88	91
12	6S6-32V-I	S-6	Candelabra Screw	32	6	1.88	91
13	6S6-48V-I	S-6	Candelabra Screw	48	6	1.88	91
14	6S6-60V-I	S-6	Candelabra Screw	60	6	1.88	91
15	6S6-75V-I	S-6	Candelabra Screw	75	6	1.88	91
16	6S6-120V-I	S-6	Candelabra Screw	120	6	1.88	91
17	6S6-130V-I	S-6	Candelabra Screw	130	6	1.88	91
18	6S6-135V-I	S-6	Candelabra Screw	135	6	1.88	91
19	6S6-145V-I	S-6	Candelabra Screw	145	6	1.88	91
20	6S6-155V-I	S-6	Candelabra Screw	155	6	1.88	91
21	6S6-230V-I	S-6	Candelabra Screw	230	6	1.88	91
22	6S6-250V-I	S-6	Candelabra Screw	250	6	1.88	91
23	6S6/7-120V-I	S-6	Intermediate Screw	120	6	1.80	93
24	6S6/7-130V-I	S-6	Intermediate Screw	130	6	1.80	93
25	6S6/DC-6V-I	S-6	D.C. Bayonet	6	6	1.81	92
26	6S6/DC-12V-I	S-6	D.C. Bayonet	12	6	1.81	92
27	6S6/DC-24V-I	S-6	D.C. Bayonet	24	6	1.81	92
28	6S6/DC-30V-I	S-6	D.C. Bayonet	30	6	1.81	92
29	6S6/DC-32V-I	S-6	D.C. Bayonet	32	6	1.81	92
30	6S6/DC-48V-I	S-6	D.C. Bayonet	48	6	1.81	92



**Fig. 91**



**Fig. 92**




**Fig. 93**

Some lamp pictures are not to scale. Filament and L.C.L. may vary by part number. For filament identification see page 6.


THE PRODUCTS SHOWN REPRESENT ONLY A SMALL PORTION OF OUR STOCK  
PLEASE CALL IF THE PRODUCT YOU NEED IS NOT LISTED  
949/452-0900 • 800/8-LIGHTS • FAX: 800-255-3141

# SPECIALTY BULBS (Continued)


Line No.	Lamp No.	Bulb Type	Base	Des. Volts	Watts	MOL (Inch)	Fig. No.
1	6S6/DC-60V-I	S-6	D.C. Bayonet	60	6	1.81	92
2	6S6/DC-75V-I	S-6	D.C. Bayonet	75	6	1.81	92
3	6S6/DC-120V-I	S-6	D.C. Bayonet	120	6	1.81	92
4	6S6/DC-130V-I	S-6	D.C. Bayonet	130	6	1.81	92
5	6S6/DC-145V-I	S-6	D.C. Bayonet	145	6	1.81	92
6	6S6/DC-155V-I	S-6	D.C. Bayonet	155	6	1.81	92
7	6S6SC-6V-I	S-6	S.C. Bayonet	6	6	1.88	94
8	6S6SC-12V-I	S-6	S.C. Bayonet	12	6	1.88	94
9	6S6SC-24V-I	S-6	S.C. Bayonet	24	6	1.88	94
10	6S6SC-36V-I	S-6	S.C. Bayonet	36	6	1.88	94
11	6S6SC-40V-I	S-6	S.C. Bayonet	40	6	1.88	94
12	6S6SC-75V-I	S-6	S.C. Bayonet	75	6	1.88	94
13	6S6SC-120V-I	S-6	S.C. Bayonet	120	6	1.88	94
14	6S6SC-130V-I	S-6	S.C. Bayonet	130	6	1.88	94
15	6S6SC-150V-I	S-6	S.C. Bayonet	150	6	1.88	94
16	6S6SC-155V-I	S-6	S.C. Bayonet	155	6	1.88	94
17	10S6-120V-I	S-6	Candelabra Screw	120	10	1.88	91
18	10S6-130V-I	S-6	Candelabra Screw	130	10	1.88	91
19	10S6/10-230V-I	S-6	Candelabra Screw	230	10	1.88	91
20	10S6/10-250V-I	S-6	Candelabra Screw	250	10	1.88	91
21	10S6/10DC-230V-I	S-6	D.C. Bayonet	230	10	1.81	92
22	10S6/10DC-250V-I	S-6	D.C. Bayonet	250	10	1.81	92
23	10S6/13-250V-I	S-6	Intermediate Screw	250	10	1.80	93
24	20S6-130V-I	S-6	Candelabra Screw	130	20	1.88	91
25	4C7-120V-I	C-7	Candelabra Screw	120	4	2.13	95
26	7C7-120V-I	C-7	Candelabra Screw	120	7	2.13	95
27	7C7-130V-I	C-7	Candelabra Screw	130	7	2.13	95
28	7C7DC-120V-I	C-7	D.C. Bayonet	120	7	2.19	96
29	10C7-120V-I	C-7	Candelabra Screw	120	10	2.13	95
30	10C7DC-120V-I	C-7	D.C. Bayonet	120	10	2.19	96




**Fig. 91**



**Fig. 94**




**Fig. 92**



**Fig. 95**



**Fig. 93**



**Fig. 96**

Some lamp pictures are not to scale. Filament and L.C.L. may vary by part number. For filament identification see page 6.

THE PRODUCTS SHOWN REPRESENT ONLY A SMALL PORTION OF OUR STOCK  
PLEASE CALL IF THE PRODUCT YOU NEED IS NOT LISTED  
949/452-0900 • 800/8-LIGHTS • FAX: 800-255-3141

# SPECIALTY BULBS (Continued)

Line No.	Lamp No.	Bulb Type	Base	Des. Volts	Watts	MOL (Inch)	Fig. No.
1	6T4-1/2/1-120V-I	T4-1/2	Candelabra Screw	120	6		97
2	6T4-1/2/1-130V-I	T4-1/2	Candelabra Screw	120	6		97
3	15T7C-120V-I	T7	Candelabra Screw	120	15	2.63	98
4	15T7DC-120V-I	T7	D.C. Bayonet	120	15		99
5	15T7DC-130V-I	T7	D.C. Bayonet	130	15		99
6	15T4C-130V-I	T4	Candelabra Screw	130	15		100
7	SR-NE120PSB	T2	Slide No. 5	120	.5		101
8	SR120V-MB	T3-1/4	Miniature Bayonet	120	2.6	1.19	102
9	SR12V-8W-MS	G4-1/2	Miniature Screw	12	8		103
10	SR130V-MB	T3-1/4	Miniature Bayonet	130	2.6	1.19	102
11	SR18V-C	T4	Candelabra Screw	18	3	1.50	100
12	SR240V-MB	T3-1/4	Miniature Bayonet	240	3-4	1.19	102
13	SR24V-C	T4	Candelabra Screw	24	2	1.50	100
14	SR24V-MB	T3-1/4	Miniature Bayonet	24	2	1.19	102
15	SR24V-MS	T3-1/4	Miniature Screw	24	2	1.19	104
16	SR30V-C	T4	Candelabra Screw	30	3	1.50	100
17	SR30V-MB	T3-1/4	Miniature Bayonet	30	2	1.19	102
18	SR48V-MS	T3-1/4	Miniature Screw	48	2	1.19	104
19	SR60V-MS	T3-1/4	Miniature Screw	60	2.4	1.19	104




Fig. 97




Fig. 98




Fig. 99




Fig. 100




Fig. 101




Fig. 102




Fig. 103




Fig. 104

Some lamp pictures are not to scale. Filament and L.C.L. may vary by part number. For filament identification see page 6.

THE PRODUCTS SHOWN REPRESENT ONLY A SMALL PORTION OF OUR STOCK  
 PLEASE CALL IF THE PRODUCT YOU NEED IS NOT LISTED  
 949/452-0900 • 800/8-LIGHTS • FAX: 800-255-3141