

HEAVY DUTY SHATTERPROOF BULBS

HEAVY DUTY SHATTERPROOF BULBS

- **Special Rubber Coating** contains glass particles should bulb break.
- **Heavy Duty** five support filament designed to withstand impact and vibration.
- **Uses:** Workshops, Garages, Construction Areas, Bathrooms ... Any Hazardous Environment.

All items NOW packaged in shatterproof "Family" packaging!



R20




BR30



A15



A21



A19 Double Pack

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./Inner Pack
25	A15	Med.	S4880	25A15/TF	Frosted	130V	2500	120	C-9	3 1/2"	Sleeve	500/25
40	A15	Med.	S4881	40A15/TF	Frosted	130V	2500	280	C-9	3 1/2"	Sleeve	500/25
60	A15	Med.	S4882	60A15/TF	Frosted	130V	2500	530	C-9	3 1/2"	Sleeve	500/25
60	A19	Med.	S3927	60A19/RS/TF	Frosted	130V	5000	520	C-9	4 1/8"	2/Pks	12
75	A19	Med.	S3928	75A19/RS/TF	Frosted	130V	5000	680	C-9	4 1/8"	2/Pks	12
100	A19	Med.	S3929	100A19/RS/TF	Frosted	130V	5000	960	C-9	4 1/8"	2/Pks	12
75	A21	Med.	S3972	75A21/TF	Frosted	130V	2500	620	C-9	5 5/16"	Sleeve	24
100	A21	Med.	S3973	100A21/TF	Frosted	130V	2500	880	C-9	5 5/16"	Sleeve	24
150	A21	Med.	S4883	150A21/TF	Frosted	130V	2500	1750	C-9	5 5/16"	Sleeve	24
50	R20	Med.	S4886	50R20/TF	Frosted	120V	2000	375	C-9	4"	Sleeve	96/12
65	BR30	Med.	S4887	65BR30/TF	Frosted	120V	2000	685	C-9	5 3/8"	Sleeve	96/12

SATCO® National Toll-Free: 1-800-43-SATCO (1-800-437-2826)

Visit Our Web Site at: www.satco.com

EXECUTIVE OFFICES & WAREHOUSE; NEW YORK, 110 Heartland Blvd., Brentwood, N.Y. 11717 • 800-437-2826 • (631) 243-2022 • FAX (631) 243-2027
 FLORIDA, 900 N.W. 159th Drive, Miami, FL 33169 • 800-437-2826 • (305) 624-2044 • FAX (305) 623-0286
 TEXAS, 2000 Valwood Parkway, Farmers Branch, TX 75234 • 800-437-2826 • (972) 247-2437 • FAX (972) 247-5408
 CALIFORNIA, 31288 San Benito St., Hayward, CA 94544 • 800-437-2826 • (510) 487-4822 • FAX (510) 487-8955
 WASHINGTON, 4710 116th St. S.W., Mukilteo, WA 98275 • 800-437-2826 • (425) 789-3300 • FAX (425) 789-3310