

Single-Use Wire Grabbers


MARCH 3, 2014 | POSTED IN [FEATURED](#) | [COMMENTS OFF](#)

Data Sheets: (MSDS, PDS, etc...):

[Load Chart](#)

[Promotional Literature](#)

[Flyer](#)



Simple- Easy-Reliable-Durable low cost single use device for pulling wire. New beveled edge for easier pulls around corners. Use once and then recycle along with scrap wire. The RectorSeal® Single-Use Wire Grabber™ is available in 18 sizes (8 AWG through 1000 mcm) to be used in sets to accommodate jobs of different sizes. Works on 600 volts through 35 KV wire and rated for both copper and aluminum wire. The lanyards are available in a variety of lengths to make staggering

QUICK LINKS

[MSDS](#)

[PDS](#)

[Contact us](#)

[About Our Company](#)

[In the news](#)

[Trade Shows](#)

[Reps: Com-Net Login](#)

[Submit Ideas](#)

[Privacy Statement](#)

[Vendor Terms & Conditions](#)

[Terms of Use](#)

[Careers](#)

[Sitemap](#)

SOCIAL

[Twitter](#)

[Facebook](#)

[YouTube](#)

multiple wire pulls effortless especially through and around nineties. The small pulling head reduces friction; therefore there is no need to oversize conduit to accommodate the pulling head.

PRODUCT DESCRIPTION	PRODUCT CODE	QTY/CS.	LBS.
SU 8 AWG Wire Grabber w/11" lanyard	98120	6	1
SU 8 AWG Wire Grabber w/15" lanyard	98117	6	1
SU 8 AWG Wire Grabber w/19" lanyard	98118	6	1
SU 8 AWG Wire Grabber w/23" lanyard	98119	6	1
SU 6 AWG Wire Grabber w/11" lanyard	98137	6	1
SU 6 AWG Wire Grabber w/15" lanyard	98138	6	1
SU 6 AWG Wire Grabber w/19" lanyard	98139	6	1
SU 6 AWG Wire Grabber w/23" lanyard	98140	6	
SU 4 AWG Wire Grabber w/11? lanyard	98133	6	1
SU 4 AWG Wire Grabber w/15? lanyard	98134	6	1
SU 4 AWG Wire Grabber w/19? lanyard	98135	6	1
SU 4 AWG Wire Grabber w/23? lanyard	98136	6	1
SU 3 AWG Wire Grabber w/11" lanyard	98129	6	1
SU 3 AWG Wire Grabber w/15" lanyard	98130	6	1
SU 3 AWG Wire Grabber w/19" lanyard	98131	6	1
SU 3 AWG Wire Grabber w/23" lanyard	98132	6	1

Blog

LANGUAGES

English

Español

中国的

Français

Deutsch

SU 2 AWG Wire Grabber w/11" lanyard	98125	6	1
SU 2 AWG Wire Grabber w/15" lanyard	98126	6	1
SU 2 AWG Wire Grabber w/19" lanyard	98127	6	1
SU 2 AWG Wire Grabber w/23" lanyard	98128	6	1
SU 1 AWG Wire Grabber w/11" lanyard	98121	6	1
SU 1 AWG Wire Grabber w/15" lanyard	98122	6	1
SU 1 AWG Wire Grabber w/19" lanyard	98123	6	1
SU 1 AWG Wire Grabber w/23" lanyard	98124	6	1
SU 1/0 AWG Wire Grabber w/14" lanyard	98141	6	1
SU 1/0 AWG Wire Grabber w/21" lanyard	98142	6	1
SU 1/0 AWG Wire Grabber w/28" lanyard	98143	6	1
SU 1/0 AWG Wire Grabber w/35" lanyard	98144	6	1
SU 2/0 AWG Wire Grabber w/14" lanyard	98145	6	2
SU 2/0 AWG Wire Grabber w/21" lanyard	98146	6	2
SU 2/0 AWG Wire Grabber w/28" lanyard	98147	6	2
SU 2/0 AWG Wire Grabber w/35" lanyard	98148	6	2
SU 3/0 AWG Wire Grabber w/14" lanyard	98149	6	2
SU 3/0 AWG Wire Grabber w/21" lanyard	98150	6	2

SU 3/0 AWG Wire Grabber w/28" lanyard	98151	6	2
SU 3/0 AWG Wire Grabber w/35" lanyard	98152	6	2
SU 4/0 AWG Wire Grabber w/14" lanyard	98153	6	2
SU 4/0 AWG Wire Grabber w/21" lanyard	98154	6	2
SU 4/0 AWG Wire Grabber w/28" lanyard	98155	6	2
SU 4/0 AWG Wire Grabber w/35" lanyard	98156	6	3
SU 250 MCM Wire Grabber w/14" lanyard	98157	6	3
SU 250 MCM Wire Grabber w/21" lanyard	98158	6	3
SU 250 MCM Wire Grabber w/28" lanyard	98159	6	3
SU 250 MCM Wire Grabber w/35" lanyard	98160	6	4
SU 300 MCM Wire Grabber w/14" lanyard	98161	6	3
SU 300 MCM Wire Grabber w/21" lanyard	98162	6	3
SU 300 MCM Wire Grabber w/28" lanyard	98163	6	4
SU 300 MCM Wire Grabber w/35" lanyard	98164	6	4
SU 350 MCM Wire Grabber w/14" lanyard	98165	6	4
SU 350 MCM Wire Grabber w/21" lanyard	98166	6	4
SU 350 MCM Wire Grabber w/28" lanyard	98167	6	4
SU 350 MCM Wire Grabber w/35" lanyard	98168	6	5

SU 400 MCM Wire Grabber w/14" lanyard	98169	6	4
SU 400 MCM Wire Grabber w/21" lanyard	98170	6	4
SU 400 MCM Wire Grabber w/28" lanyard	98171	6	4
SU 400 MCM Wire Grabber w/35" lanyard	98172	6	5
SU 500 MCM Wire Grabber w/14" lanyard	98173	6	5
SU 500 MCM Wire Grabber w/21" lanyard	98174	6	4
SU 500 MCM Wire Grabber w/28" lanyard	98175	6	6
SU 500 MCM Wire Grabber w/35" lanyard	98176	6	6
SU 600 MCM Wire Grabber w/14" lanyard	98177	6	6
SU 600 MCM Wire Grabber w/21" lanyard	98178	6	6
SU 600 MCM Wire Grabber w/28" lanyard	98179	6	6
SU 600 MCM Wire Grabber w/35" lanyard	98180	6	7
SU 750 MCM Wire Grabber w/14" lanyard	98181	6	7
SU 750 MCM Wire Grabber w/21" lanyard	98182	6	7
SU 750 MCM Wire Grabber w/28" lanyard	98183	6	7
SU 750 MCM Wire Grabber w/35" lanyard	98184	6	8
SU 1000 MCM Wire Grabber w/14" lanyard	98185	6	8

SU 1000 MCM Wire Grabber w/21" lanyard	98186	6	8
SU 1000 MCM Wire Grabber w/28" lanyard	98187	6	8
SU 1000 MCM Wire Grabber w/35" lanyard	98188	6	8

RectorSeal® 2601 Spenwick Drive Houston TX 77055 Tel : 713-263-8001 / 800-231-3345 Fax : 713-263-7577 / 800-441-0051