

PRO-WEAR® PERSONAL PROTECTION EQUIPMENT KITS

40 CAL/CM² HRC 4



► SALISBURY PRO-WEAR® ARC FLASH PERSONAL PROTECTION EQUIPMENT KITS ARE AVAILABLE IN AN ATPV RATING OF 40 CAL/CM². This kit contains an arc flash coat, bib overalls, PRO-HOOD®, hard hat, SKBAG, and safety glasses.

NEW 2-COLOR PRO-WEAR ARC FLASH PROTECTION PPE KITS AVAILABLE.

Sizes S, M, L, XL, 2XL, and 3XL available from stock. Other sizes and orange color available by special order.

THESE KITS MEET NFPA 70E
HAZARD RISK CATEGORY 4.

**LIGHTER MATERIAL THAN EVER.
40 CAL/CM² "LT" MATERIAL OFFERS
EXTREMELY LIGHTWEIGHT OPTION.**



NEW



If You Need it, Request it.
Call customer service if you need something not seen here.

PRODUCT NUMBERING CHART FOR 40 CAL/CM² PPE KITS

Salisbury Cat. No.	Size of Garments (choose one below)	ATPV Rating cal/cm ²	HRC	Description
SK40	S, M, L, XL, 2XL, 3XL	40	4	gray kit
SK40TC	S, M, L, XL, 2XL, 3XL	40	4	2-color
SK40LT	S, M, L, XL, 2XL, 3XL	40	4	lightweight
Example: SK40	2XL	40	4	

SK402XL is an extra extra large clothing kit with a rating of 40 cal/cm² that

NOTE: Available in orange upon request. Contact your local Salisbury Representative.
OPTION: Add suffix "-BP" to replace the SKBAG Large Storage Bag with a SKBACKPACK Specialty Reinforced Back Pack.

NEW

PREFER A BACKPACK WITH YOUR KIT?

Make any kit a Back Pack kit,
by adding suffix "-BP" to you part number
or contacting your local Salisbury by
Honeywell representative for more.



ALL PRO-WEAR® ARC FLASH PROTECTION CLOTHING KITS

SIZING

SALISBURY PRO-HOOD® ARC FLASH PROTECTION HOODS ARE SIZED ONE SIZE FITS ALL.

PRODUCT: COATS & JACKETS


Measurements in inches (minimum allowed)	
CHEST	COAT/JACKET SIZE
34-36"	S
38-40"	M
42-44"	L
46-48"	XL
50-52"	2XL
54-56"	3XL
SPECIAL ORDER SIZES	
58-60"	4XL
62-64"	5XL

PRODUCT: BIB OVERALLS & OVERPANTS

Measurements in inches (minimum allowed)		
WAIST	BIB/OVERPANTS SIZE	INSEAM
28-30"	S	28"
32-34"	M	29"
36-38"	L	30"
40-42"	XL	30"
44-46"	2XL	30"
48-50"	3XL	30"
SPECIAL ORDER SIZES		
52-54"	4XL	30"
56-58"	5XL	30"

PRODUCT: COVERALL

Measurements in inches (minimum allowed)		
CHEST	COVERALL SIZE	INSEAM
34-36"	S	28"
38-40"	M	29"
42-44"	L	30"
46-48"	XL	30"
50-52"	2XL	30"
54-56"	3XL	30"
SPECIAL ORDER SIZES		
58-60"	4XL	30"
62-64"	5XL	30"



HOW TO MEASURE

- A** Chest - Measure around body at the underarm area
- B** Waist - Measure around waist at the largest area
- C** Inseam - Measure from mid crotch down to leg hem

ALL PRO-WEAR® ARC FLASH PROTECTION CLOTHING KITS

MATERIAL WEIGHTS

PRODUCT FEATURE

THE SALISBURY ADVANTAGE

LIGHTER MATERIAL MAKES ALL THE DIFFERENCE

THE SALISBURY 40 CAL/CM² LT ARC FLASH MATERIAL MAKES WORKING MORE COMFORTABLE THEN EVER.

Salisbury has made it even easier to do your job safely and comfortably. Salisbury offers an even lighter 40 cal/cm² option with our LT line. The 40 cal/cm² LT option is 10% lighter than the standard 40 cal/cm² material making your job even more comfortable.

MATERIAL WEIGHT FOR ATPV RATINGS

ATPV Rating cal/cm ²	Material Weight oz./yd ²
8	7 oz./yd ² (237 g/m ²)
12	9 oz./yd ² (305 g/m ²)
20	13 oz./yd ² (441 g/m ²)
31	2 layers - 9 oz./yd ² (305 g/m ²) & 7 oz./yd ² (237 g/m ²)
40	2 layers - 13 oz./yd ² (441 g/m ²) & 5.5 oz./yd ² (186 g/m ²)
40-LT	10% LIGHTER 4 layers - 7 oz./yd ² (237 g/m ²) & 5.5 oz./yd ² (186 g/m ²) & 2 layers - 1.9 oz./yd ² (64 g/m ²)
55	2 layers - 13 oz./yd ² (441 g/m ²) & 13 oz./yd ²
75	3 layers - 2 layers 13 oz./yd ² (441 g/m ²) & 1 layer 7 oz./yd ² (237 g/m ²)
100	3 layers - 10 oz./yd ² (339 g/m ²) & 2 layers 9.4 oz./yd ² (319 g/m ²)