



Table 19.129: Non-Illuminated Trigger Action Emergency Stop Push Buttons, Ø 40 mm (Red) (screw clamp terminal connections)

Shape of Head	Type of Push	Type of Contact		Catalog Number	Components
		N.O.	N.C.		
	Trigger action push-pull [42]	1	1	XB5AT845	(ZB5AZ105 + ZB5AT84)
	Trigger action turn-to-release [42]	1	1	XB5AS8445	(ZB5AZ105 + ZB5AS844)
		—	2	XB5AS8444	(ZB5AZ104 + ZB5AS844)
	Trigger action Key release (No. 455) [42]	1	1	XB5AS9445	(ZB5AZ105+ ZB5AS944)
	Trigger action Push-pull [42]	—	1	XB5AT842	(ZB5AZ102 + ZB5AT84)
	Trigger action Turn-to-release [42]	—	1	XB5A8442	(ZB5AZ102 + ZB5AS844)
	Trigger action Key release (No. 455) [42]	—	1	XB5AS9442	(ZB5AZ102 + ZB5AS944)

Table 19.130: Non-Illuminated Selector Switches and Key Switches (screw clamp terminal connections) [43]



Shape of Head	Type of Operator	Type of Contact		Number and Type of Positions	Catalog Number	Components
		N.O.	N.C.			
	Standard lever, black	1	—	2-maintained	XB5AD21	(ZB5AZ101 + ZB5AD2)
		1	1	2-maintained	XB5AD25	(ZB5AZ105 + ZB5AD2)
		2	—	3-maintained	XB5AD33	(ZB5AZ103 + ZB5AD3)
3-momentary to center	XB5AD53			(ZB5AZ103 + ZB5AD5)		
	Extended lever, black	1	—	2-maintained	XB5AJ21	(ZB5AZ101 + ZB5AJ2)
		2	—	3-maintained	XB5AJ33	(ZB5AZ103 + ZB5AJ3)
				3-momentary to center	XB5AJ53	(ZB5AZ103 + ZB5AJ5)
	Key (No. 455)	1	—	2-maintained	XB5AG21	(ZB5AZ101 + ZB5AG2)
				2-momentary to left	XB5AG61	(ZB5AZ101 + ZB5AG6)
		2	—	3-maintained	XB5AG03	(ZB5AZ103 + ZB5AG0)
					XB5AG33	(ZB5AZ103 + ZB5AG3)
				3-maintained		

NOTE: The symbol indicates key withdrawal position(s).

For Legends, see [XB5 Legend Holders](#), page 19-58 and [XB5 Legend Inserts Only](#), page 19-59

[42] Trigger action mushroom heads are tamper proof in that a change of contact state is not possible by teasing or floating the operator. For emergency stop applications, always use a trigger action push button (per EN/IEC 13850).

[43] For contact configurations, see [Table 19.144 Sequence of Contacts on Selector Switch Bodies](#), page 19-50.