


Table 26.14: 26.14: Options—Field Installed (continued)

Description		For Use on Drives		Catalog No.		
 <p>Flange Kit</p> <p>Kit includes: a metal frame, seals, mounting hardware, and a bracket to mount the fan kit so the fan can be accessed from the front of the drive template. Kit used to mount the heatsink of the drive outside of an enclosure.</p> <p>VW3A9506</p>	ATV61/71H037M3...HU15M3			VW3A9501		
	ATV61/71H075N4...HU22N4					
	ATV61/71HU22M3...HU40M3					
	ATV61/71HU30N4...HU40N4				VW3A9502	
	ATV61/71HU55M3					
	ATV61/71HU55N4, HU75N4				VW3A9503	
	ATV61/71HU75M3				VW3A9504	
	ATV61/71HD11N4					
	ATV61/71HD11M3X...HD15M3X				VW3A9505	
	ATV61/71HD15N4, HD18N4					
	ATV61/71HD18M3X...HD22M3X				VW3A9506	
	ATV61/71HD22N4, ATV61/71HU30Y...HD30Y					
	ATV61/71HD30N4, HD37N4				VW3A9507	
	ATV61/71HD30M3X...HD45M3X				VW3A9508	
	ATV61/71HD45N4...HD75N4, ATV61/71HD37Y...HD90Y					
	ATV61HD55M3X...HD75M3X				VW3A9509	
	ATV61HD90N4...HC11N4					
	ATV71HD55M3X, ATV71HD90N4				VW3A9510	
	ATV61HD90M3X, ATV61HC13N4					
	ATV71HD75M3X, ATV71HC11N4				VW3A9511	
	ATV61HC16N4, ATV61HC20Y, ATV61/71HC11Y...HC16Y, ATV71HC13N4					
	ATV61HC22N4, ATV71HC16N4				VW3A9512	
	ATV61HC25N4...HC31N4				VW3A9513	
	ATV61HC40Y					
	ATV61/71HC25Y, HC31Y				VW3A9514	
	ATV71HC20N4...HC28N4					
	ATV71HC20Y				VW3A9515	
	ATV61HC25N4...HC31N4 with VW3A7101 braking transistor					
	ATV61HC40Y				VW3A9516	
	ATV61/71HC25Y, HC31Y					
	ATV71HC20N4...HC28N4 with VW3A7101 braking transistor					
	ATV71HC20Y					
	<p>Type 1 Conduit Kit</p> <p>Kit includes: a metal box with conduit knockouts. The kit provides conduit landing when wall mounting the drive.</p>	ATV61/71H037M3...HU15M3				VW3A9201
		ATV61/71H075N4...HU22N4				
		ATV61/71HU22M3...HU40M3				
ATV61/71HU30N4...HU40N4					VW3A9203	
ATV61/71HU55M3						
ATV61/71HU55N4, HU75N4				VW3A9204		
ATV61/71HU75M3						
ATV61/71HD11N4				VW3A9205		
ATV61/71HD11M3X...HD15M3X						
ATV61/71HD15N4, HD18N4				VW3A9206		
ATV61/71HD18M3X...HD22M3X						
ATV61/71HD22N4				VW3A9207		
ATV61/71HU30Y...HD30Y						
ATV61/71HD30N4, HD37N4				VW3A9208		
ATV61/71HD30M3X...HD45M3X				VW3A9209		
ATV61/71HD45N4...HD75N4						
ATV61/71HD37Y...HD90Y				VW3A9210		
ATV61HD55M3X...HD75M3X						
ATV61HD90N4...HC11N4				VW3A9211		
ATV71HD55M3X, ATV71HD90N4, ATV61HC11N4						
ATV61HD90M3X, ATV61HC13N4				VW3A9212		
ATV71HD75M3X, ATV71HC11N4						
ATV61HC16N4, ATV71HC13N4				VW3A9213		
ATV61/71HC11Y...HC16Y						
ATV61HC20Y				VW3A9214		
ATV61HC22N4, ATV71HC16N4						
ATV61HC25N4...ATV61HC31N4				VW3A9215		
ATV71HC20N4...HC28N4						
ATV71HC20Y				VW3A9216		
ATV61/71HC25Y, HC31Y						
ATV61HC40Y						
ATV61HC25N4...HC31N4 with VW3A7101 braking transistor						
ATV71HC20N4...HC28N4 with VW3A7101 braking transistor						
ATV71HC20Y						
ATV61/71HC25Y, HC31Y						
ATV61HC40Y						
<p>Profibus Option Card Cover</p> <p>Type 1 cover for Profibus Option Card</p>	230 V Drive controllers		480 V Drive controllers		VW3A9201PF	
	ATV61H**** [46]	ATV71H****	ATV61H****	ATV71H****		
	075M3	037M3	075N4	075N4		
	U15M3	075M3	U15N4	U15N4		
	—	U15M3	U22N4	U22N4		
	U22M3	U22M3	U30N4	U30N4		
	U30M3	U30M3	U40N4	U40N4		
	U40M3	U40M3	—	—		
	U55M3	U55M3	U55N4	U55N4		
	—	—	U75N4	U75N4		
	U75M3	U75M3	D11N4	D11N4		
	D11M3X	D11M3X	D15N4	D15N4		
	D15M3X	D15M3X	D18N4	D18N4		

[46] The symbol "*" indicates the part of the number that varies with controller size or rating.