

XB4 Complete Devices—Illuminated

Table 19.69: Pilot Lights with Protected LED™ (screw clamp terminal connections) [3]




XB4BV5

Shape of Head	Supply Voltage	Color	Catalog Number	Components
	24 Vac/Vdc	White	XB4BVB1	(ZB4BVB1 + ZB4BV013)
		Green	XB4BVB3	(ZB4BVB3 + ZB4BV033)
		Red	XB4BVB4	(ZB4BVB4 + ZB4BV043)
		Yellow	XB4BVB5	(ZB4BVB5 + ZB4BV053)
		Blue	XB4BVB6	(ZB4BVB6 + ZB4BV063)
		White	XB4BVG1	(ZB4BVG1 + ZB4BV013)
	110–120 Vac	Green	XB4BVG3	(ZB4BVG3 + ZB4BV033)
		Red	XB4BVG4	(ZB4BVG4 + ZB4BV043)
		Yellow	XB4BVG5	(ZB4BVG5 + ZB4BV053)
		Blue	XB4BVG6	(ZB4BVG6 + ZB4BV063)

Table 19.70: Pilot Lights for BA9s Bulb (screw clamp terminal connections)




XB4BV64



XB4BV33

Shape of Head	Supply Voltage	Color	Catalog Number	Components
Direct supply, for BA9s (incandescent, LED, neon) V < 250 V, 2.4 W bulb (bulb not included)				
	< 250 Vac/Vdc	White	XB4BV61	(ZB4BV6 + ZB4BV01)
		Green	XB4BV63	(ZB4BV6 + ZB4BV03)
		Red	XB4BV64	(ZB4BV6 + ZB4BV04)
		Yellow	XB4BV65	(ZB4BV6 + ZB4BV05)
Transformer type with 1.2 VA, 6 V secondary. BA9s incandescent bulb included				
	110–120 Vac 50/60 Hz	White	XB4BV31	(ZB4BV3 + ZB4BV01)
		Green	XB4BV33	(ZB4BV3 + ZB4BV03)
		Red	XB4BV34	(ZB4BV3 + ZB4BV04)
		Yellow	XB4BV35	(ZB4BV3 + ZB4BV05)

Table 19.71: Illuminated Push Buttons, Momentary (screw clamp terminal connections) [3]



XB4BW33B5



XB4BW3465



XB4BW3545

Shape of Head	Description	Type of Contact		Supply Voltage	Color of Push	Catalog Number	Components	
		N.O.	N.C.					
Flush								
	Protected LED	1	1	24 Vac/Vdc	White	XB4BW31B5	(ZB4BW0B15 + ZB4BW313)	
					Green	XB4BW33B5	(ZB4BW0B35 + ZB4BW333)	
					Red	XB4BW34B5	(ZB4BW0B45 + ZB4BW343)	
					Yellow	XB4BW35B5	(ZB4BW0B55 + ZB4BW353)	
					Blue	XB4BW36B5	(ZB4BW0B65 + ZB4BW363)	
					110–120 Vac	White	XB4BW31G5	(ZB4BW0G15 + ZB4BW313)
						Green	XB4BW33G5	(ZB4BW0G35 + ZB4BW333)
						Red	XB4BW34G5	(ZB4BW0G45 + ZB4BW343)
				Yellow		XB4BW35G5	(ZB4BW0G55 + ZB4BW353)	
				Blue		XB4BW36G5	(ZB4BW0G65 + ZB4BW363)	
				< 250 Vac/Vdc		White	XB4BW3165	(ZB4BW065 + ZB4BW31)
					Green	XB4BW3365	(ZB4BW065 + ZB4BW33)	
					Red	XB4BW3465	(ZB4BW065 + ZB4BW34)	
					Yellow	XB4BW3565	(ZB4BW065 + ZB4BW35)	
110–120 Vac 50/60 Hz	White	XB4BW3135	(ZB4BW035 + ZB4BW31)					
	Green	XB4BW3335	(ZB4BW035 + ZB4BW33)					
	Red	XB4BW3435	(ZB4BW035 + ZB4BW34)					
	Yellow	XB4BW3535	(ZB4BW035 + ZB4BW35)					
	230–240 Vac 50/60 Hz	White	XB4BW3145	(ZB4BW045 + ZB4BW31)				
		Green	XB4BW3345	(ZB4BW045 + ZB4BW33)				
Red		XB4BW3445	(ZB4BW045 + ZB4BW34)					
	Protected LED	1	1	24 Vac/Vdc	White	XB4BW11B5	(ZB4BW0B15 + ZB4BW113)	
					Green	XB4BW13B5	(ZB4BW0B35 + ZB4BW133)	
					Red	XB4BW14B5	(ZB4BW0B45 + ZB4BW143)	
					Yellow	XB4BW15B5	(ZB4BW0B55 + ZB4BW153)	
					Blue	XB4BW16B5	(ZB4BW0B65 + ZB4BW163)	
					110–120 Vac	White	XB4BW11G5	(ZB4BW0G15 + ZB4BW113)
						Green	XB4BW13G5	(ZB4BW0G35 + ZB4BW133)
						Red	XB4BW14G5	(ZB4BW0G45 + ZB4BW143)
				Yellow		XB4BW15G5	(ZB4BW0G55 + ZB4BW153)	
				Blue		XB4BW16G5	(ZB4BW0G65 + ZB4BW163)	

For legends, refer to XB4 Legend Holders, page 19-38, XB4 Legend Inserts, page 19-39, and XB4 Legend Sheets, page 19-39.

[3] For 240 V LED, replace the last “B” or “G” in the catalog number with an “M”. For example, XB4BVB1 (24 V) becomes XB4BVM1 (240 V—AC only).