

XAC Operators and Accessories

Table 19.397: Operators [11]



Description	Color	Catalog Number
Booted push button	White	XACA9411
	Black	XACA9412
	Green	XACA9413
	Red	XACA9414
	Yellow	XACA9415
	Blue	XACA9416
	Brown	XACA9419

Table 19.398: Mushroom Operators



Description	Mushroom Size	Color	Catalog Number
Mushroom head, push to maintain/turn-to-release (trigger action)[12]	30 mm	Red	ZA2BS834
	40 mm	Red	ZA2BS844
Mushroom head, push to maintain/key turn-to-release (trigger action)[12]	40 mm	Red	ZA2BS944



Table 19.399: Selector Switches and Wobble Stick



Description	Color	Catalog Number
Selector switch/2 position—maintained[13]	Black	ZA2BD2
Selector switch/3 position—maintained[13]	Black	ZA2BD3
Selector switch/2 position—maintained key operated—key removal from LT or RT position[13]	NA	ZA2BG4
Selector switch/3 position—maintained key operated—key removal from LT or RT position[13]	NA	ZA2BG5
Wobble stick (bottom mounting recommended)	Black	ZA2BB2



Table 19.400: Pilot Light Components

Description	Color	Catalog Number
Direct supply base/without lamp (for 6 to 120 V applications) (AC/DC) [14]	—	ZB2BV006

Table 19.401: Enclosure Accessories



Description	Catalog Number
Blank hole plug	ZB2SZ3
Mechanical interlock (momentary). For use with XAC booted operators only	XACA009
Screw adapter for self-supporting cable	XACB961
Low suspension ring for single row station	XACA971
Protective guard for bottom mounted mushroom head	XACA982
Protective guard for bottom mounted selector switch or key switch	XACA983




Table 19.402: Lamps, BA9s Base

Type	Voltage	Watts	Catalog Number
Replacement bulbs (Type BA9s) Incandescent	6 Vac/Vdc	1.2	DL1CB006
	12 Vac/Vdc	2.0	DL1CE012
	24 Vac/Vdc	2.0	DL1CE024
	48 Vac/Vdc	2.4	DL1CE048
	130 Vac/Vdc	2.6	DL1CE130





Table 19.403: LED, BA9s Base

Type	Color	Voltage	Catalog Number
LED, BA9s base for Direct Supply blocks	Green	6 Vac/Vdc	DL1CJUS0063
	Red	6 Vac/Vdc	DL1CJUS0064
	Amber	6 Vac/Vdc	DL1CJUS0065
	Green	24 Vac/Vdc	DL1CJUS0243
	Red	24 Vac/Vdc	DL1CJUS0244
	Amber	24 Vac/Vdc	DL1CJUS0245
	White	24 Vac/Vdc	DL1CJUS0241
	Blue	24 Vac/Vdc	DL1CJUS0246
	Green	120 Vac/Vdc	DL1CJUS1203
	Red	120 Vac/Vdc	DL1CJUS1204
	Amber	120 Vac/Vdc	DL1CJUS1205

[11] Booted push buttons are for cover mounting only. All other operators can be mounted on cover or bottom.
 [12] Trigger action mushroom heads are tamper proof in that a change of contact state is not possible by teasing or floating the operator.
 [13] Not for use with XENG contact blocks.
 [14] see Table 19.402 Lamps, BA9s Base, page 19-129 and Table 19.403 LED, BA9s Base, page 19-129.