

# Meter Sockets



RJ193AX



RJ103AX



RJ102CXJ

## 135 Amp Continuous Meter Mounting Equipment— Ringless Type, 1 Phase, 3 Wire, 600V 1 Position Residential

Catalog Number	Dimensions (inches)			Amps	Cont. Service	Wire Range	No. of Jaws	5th Jaw	Hub	KO Fig.	List Price \$	Notes
	H	W	D									
<b>HORN BYPASS</b>												
RJ192PX	11.7	8.0	3.6	135	OH/UG	#14-2/0	4	EC659-0121	RX Opening	1	85.00	①
RJ193AX	11.7	8.0	3.6	135	OH/UG	#14-2/0	4	EC659-0121	RX Opening	1	92.00	
RJ193CXJ	11.7	8.0	3.6	135	OH/UG	#14-2/0	5	EC659-0121	RX Opening	1	88.00	②
RJ192AC	11.7	8.0	3.6	135	OH/UG	#14-2/0	4	EC659-0121	1-½" Hub Installed	1	91.00	
<b>NO BYPASS</b>												
RJ103AC	11.7	8.0	3.6	135	OH/UG	#14-2/0	4	EC659-0121	1-½" Hub Installed	1	89.00	
RJ102CXJ	11.7	8.0	3.6	135	OH/UG	#14-2/0	5	Installed	RX Opening	1	86.00	①
RJ103AX	11.7	8.0	3.6	135	OH/UG	#14-2/0	4	EC659-0121	RX Opening	1	79.00	
RJ103AXF	11.7	8.0	3.6	135	OH/UG	#14-2/0	4	EC659-0121	RX Opening	1	79.00	②③
RN102A	11.7	8.0	3.6	135	UG	#14-2/0	4	EC659-0121	None	1	85.00	

## 135 Amp Continuous Meter Mounting Equipment— Ring Type, 1 Phase, 3 Wire, 600V 1 Position Residential

Catalog Number	Dimensions (inches)			Amps	Cont. Service	Wire Range	No. of Jaws	5th Jaw	Hub	KO Fig.	List Price \$	Notes
	H	W	D									
<b>NO BYPASS</b>												
SN152CX	11.7	8.0	3.6	135	OH	#14-2/0	5	Installed	RX Opening	1	92.00	④
SN152CC	11.7	8.0	3.6	135	OH/UG	#14-2/0	5	Installed	1-½" Hub Installed	1	106.00	④
SJ102AX	11.7	8.0	3.6	135	OH/UG	#14-2/0	4	EC659-0121	RX Opening	1	77.00	④
SJ102AC	11.7	8.0	3.6	135	OH/UG	#14-2/0	4	EC659-0121	1-½" Hub Installed	1	78.00	④
SN102A	11.7	8.0	3.6	135	UG	#14-2/0	4	EC659-0121	None	1	85.00	④
SN152C	11.7	8.0	3.6	135	UG	#14-2/0	5	Installed	None	1	92.00	④

Contact utility or sales office for approval by your local utility prior to installation.

All devices listed on this page include (2) ground lugs

- ①7/16" Barrel lock knockout
- ②7/8" Barrel lock knockout
- ③Stainless steel latch and hasp
- ④Sealing ring included