



Job Name:

Job Type:

Comments:

Quantity:

98860SW-787: LED Disk Light, 170 lumens, 4watt, 3000K, 85CRI



Dimensions:

Diameter: 3"

Wire: 36" (color/Black)

Height: 5/8"

Mounting Proc.: Mounting Strap

Connection: Both

Features:

- The advanced LED technology in Sea Gull Lighting products is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

Material List:

Safety Listing:

cETL Listed

Instruction Sheets:

English (HC-1887FS)

Trilingual (English, Spanish, and French) (HC-1887FS)

Collections: Ambiance® LED Disk Lighting (Primary)
Ambiance® LED Under Cabinet

3" diameter LED disk light in bronze finish, requires 12V transformer for operation (sold separately). Order plug-in 30W zero-load electronic transformer with 8' output cord (98640S-12)

170 lumens, 4 watts, 42 lumens per watt

Includes 36" lead wire for connection to additional LED disks, optional mounting hub or Ambiance Lx system via fused plug

Increase light output up to 240 lumens per disk by powering with 12VDC power supply

The look, feel and performance of halogen/xenon pucks while reducing energy and operating cost by up to 80%

Delivers light output of 170 lumens using only 4 watts for efficacy of 42 lumens per watt

Contains 3 integrated multi-LED Nichia LED chip packages

Long 40,000 hours life - last 20X's longer than halogen for maintenance free operation

12VAC/12VDC

Dimmable with wide range on incandescent and electronic low voltage dimmers on 12V electronic and magnetic transformers

Configurable and linkable for easier multiple unit installations. Daisy chain up to 6 disks from one to another or hub and spoke mount using optional mounting hub

Color accurate illumination 85CRI, 3000K

Low profile, aluminum housing for cooler operation and maximum LED life

Available in 3 painted finishes; white, black, bronze and (plated) tinted aluminum

Surface or recessed mounting

Can be connected to and dimmed using 12VAC Ambiance Lx linear lighting system with optional fused plug 9488-12/15

UPC #:785652153136

Finish: Plated Bronze (787)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	98860SW-787	1	785652153136	3.75	3.75	1.37	0.011	0.2	Yes
Master Pack	98860SW-787	5	10785652153133	4.25	4.25	6.25	0.065	1.3	Yes
Shipping Master		75	20785652153130	21.5	9	14	1.568	21.9	Yes