



Job Name:

Job Type:

Comments:

Quantity:

98860SW-986: LED Disk Light, 170 lumens, 4watt, 3000K, 85CRI



Dimensions:

Diameter: 3" **Wire:** 36" (color/Black)
Height: 5/8" **Connection:** Both

Features:

- The advanced LED technology in Sea Gull Lighting products is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

Material List:

Safety Listing:

cETL Listed for Damp Locations

Instruction Sheets:

English (HC-1887FS)
Trilingual (English, Spanish, and French) (HC-1887FS)

Collections: Ambiance® LED Disk Lighting (Primary)
Ambiance® LED Under Cabinet

3" diameter LED disk light in tinted aluminum finish, requires 12V transformer for operation (sold separately). Order plug-in 30W zero-load electronic transformer with 8' output cord (98640S-12)

170 lumens, 4 watts, 42 lumens per watt

Increase light output up 240 lumens by powering with 12VDC power supply.

The look, feel and performance of halogen/xenon pucks while reducing energy and operating cost by up to 80

Delivers light output of 170 lumens using only 4 watts for efficacy of 42 lumens per watt, 12VAC

Contains 3 integrated multi-LED Nichia LED chip packages

Long 40,000 hours life - last 20X's longer than halogen for maintenance free operation

Includes 36" lead wire for connection to additional LED disks, optional mounting hub or Ambiance Lx system via fused plug

12VAC/12VDC

Dimmable with wide range on incandescent and electronic low voltage dimmers on 12V electronic and magnetic transformers

Configurable and linkable for easier multiple unit installations. Daisy chain up to 6 disks from one to another or hub and spoke mount using optional mounting hub

Color accurate illumination 85CRI, 3000K

Low profile, aluminum housing for cooler operation and maximum LED life

Available in 4 painted finishes; white, black, bronze and tinted aluminum finish

Surface or recessed mounting

Can be connected to and dimmed using 12VAC Ambiance Lx linear lighting system with optional fused plug 9488-12/15

UPC #:785652153129

Finish: Tinted Aluminum (986)

Shipping Information:

| Package Type | Product # | Quantity | UPC | Length | Width | Height | Cube | Weight | UPS Ship |
|-----------------|-------------|----------|----------------|--------|-------|--------|-------|--------|----------|
| Individual | 98860SW-986 | 1 | 785652153129 | 3.75 | 3.75 | 1.75 | 0.014 | 0.2 | Yes |
| Master Pack | 98860SW-986 | 5 | 10785652153126 | 4.25 | 4.25 | 6.25 | 0.065 | 1.3 | Yes |
| Shipping Master | | 100 | 20785652153123 | 21.5 | 9 | 14 | 1.568 | 27.8 | Yes |