



Home > Tools > Cordless Tools > Cordless Lighting > Flashlights > DCL040



DCL040
20V MAX* Lithium Ion LED Work Light
5 of 5 (12 reviews)

[View Reviews](#)

[Buy Now](#) Find a Local Retailer [>](#)

[Add to Wish List >](#)

[Add to Reorder list >](#)

Product Features

- Bright LED output - 110 Lumens
- Integral hook for hands free use in multiple placements
- Head rotates 120°
- Low heat output compared to Xenon lights
- Efficient LED bulb improves run-time

Share

8+1 0

Like 2

Tweet 0

review >

Already Own This Product? [Register >](#)
[Write a Review >](#)

Need a part for this product? [>](#)

Documentation for this product

Search For DCL040 Part [>](#)



*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

PRODUCT TOUR

ATTACHMENTS

DCB201



4 of 5

DCB200



4.5 of 5

DCB203



5 of 5

DCB204



Not rated yet

SPECS & WARRANTY

QUESTIONS & ANSWERS

USER REVIEWS (12)

Specifications

Voltage	20V MAX*
Bulb Type	LED
Run-Time	11hrs
Tool Weight	1.0lbs
Shipping Weight	1.0lbs
Power Source	
Brightness	Lumens
Charge Time	

Warranty Information

This DEWALT® High Performance Industrial Tool comes with a warranty package that includes:

- 3 Year Limited Warranty
- 1 Year Free Service Contract
- 90 Day Money Back Guarantee

More information on the general DEWALT warranty

DCL040 Includes:

- *Battery NOT included

RELATED TOOLS

DCF610S2



12V MAX* 1/4" Screwdriver Kit

4.5 of 5 (20 reviews)

DCF815S2



12V MAX* 1/4" Impact Driver Kit

5 of 5 (23 reviews)

DCD710S2



12V MAX* 3/8" Drill Driver Kit

4.5 of 5 (23 reviews)

DCT410S1



12V MAX* 17mm Inspection Camera with Wireless Screen Kit

4 of 5 (15 reviews)

DCT414S1

5 of 5 (3 reviews)

12V MAX* Infrared Thermometer Kit



COPYRIGHT© 2014 DEWALT. All Rights Reserved. The following are trademarks for one or more DEWALT Power Tools and Accessories: The yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

**GUARANTEED
TOUGH.®**

Follow Us:    [Privacy/Security](#) | [DEWALT Legal](#) | [Safe Travel with Cordless Tools](#) | [Global](#) | [Company Information](#) | [IMPORTANT SAFETY RECALLS](#)