



HEAVY-DUTY POWER TOOLS

GUARANTEED TOUGH.



Worksite Radio/Charger

WORKSITE RADIO/CHARGER

SPECIFICATIONS		DC011
Power Source		7.2V to 18V Battery or AC Power
Radio Output		92 dB
AM/FM Digital Tuner		Yes
Auxiliary Port		Yes
Charge Time		1 hour or less
Tool Weight		13.2 lbs



Cordless/Corded Worklight/Dual Port Charger w/GFCI Protection

WORKLIGHT/CHARGER

SPECIFICATIONS		DC022
Power Source		12-18V Batteries or AC Power
Bulb		38W Fluorescent
Brightness		2700 Lumens
Charge Time		1 Hour or less
Run-Time		1-hour on 18V DC9096 Battery
Weight		12.0 lbs
Batteries		Sold Separately



18V Cordless Fluorescent Area Light



14.4V/12V Cordless Fluorescent Area Light

FLUORESCENT AREA LIGHTS

SPECIFICATIONS		DC527	DC528
Voltage		18V	14.4V OR 12V
Bulb		13 Watt	13 Watt
Run-Time		3.5 hrs	2.75 hrs
Weight		1.25 lbs	1.15 lbs
Battery		Sold Separately	Sold Separately



36V Cordless Floodlight



18V Cordless Flexible Floodlight



14.4V Cordless Flexible Floodlight

XENON FLOODLIGHTS

SPECIFICATIONS		DC509	DW919	DW918
Voltage		36V	18V	14.4V
Bulb		Xenon	Xenon	Xenon
Run-Time		8 hrs	3 hrs	3 hrs
Weight		1.14 lbs	.75 lbs	0.5 lbs
Battery		Sold Separately	Sold Separately	Sold Separately



18V Cordless Pivoting Head Flashlight



14.4V Cordless Pivoting Head Flashlight



12V Cordless Pivoting Head Flashlight

FLASHLIGHTS

SPECIFICATIONS		DW908	DW906	DW904
Voltage		18V	14.4V	12V
Bulb		Xenon	Xenon	Xenon
Run-Time		3 hrs	3 hrs	3 hrs
Tool Weight		0.5 lbs	0.5 lbs	0.5 lbs
Batteries		Sold Separately	Sold Separately	Sold Separately



1 Hour Charger w/ Auto. Tune-Up™ Mode



Dual Port 1 Hour Charger



15 Minute Charger



Worksite Radio/Charger



1 Hour Fan Cooled Charger



1 Hour Charger



1 Hour Vehicle Charger



1 Hour Fan Cooled Vehicle Charger

BATTERIES / CHARGERS

CAT #	VOLTAGE	DW9116	DW9216	DW9117	DC011	DW0246	DC9000	DW9109	DW0249
DC9360	36V	X	X	X	X	X	X	X	X
DW0242	24V	X	X	X	X	60	X	X	60
DC9096	18V	60	60	20	60	X	X	60	X
DC9091	14.4V	60	60	20	60	X	X	60	X
DC9071	12V	60	60	20	60	X	X	60	X
DW9061	9.6V	45	45	15	45	X	X	45	X
DW9057	7.2V	30	30	12	30	X	X	30	X

www.DeWALT.com

1-800-4 DeWALT

<PREVIOUS

5
NEXT>