





Strion® LED Rechargeable Flashlight

| FL 1 STANDARD | HIGH | MEDIUM | LOW |
|---|----------------------|---------------------|---------------------|
|  | 160 LUMENS | 80 LUMENS | 40 LUMENS |
|  | 2h | 4h | 7h 30min |
|  | 200m | 141m | 100m |
|  | 10,000cd | 5,000cd | 2,500cd |



Case Material: 6000 series machined aircraft aluminum with anodized finish.

Dimensions: Length: 5.90 in. (14.99 cm) Head Diameter: 1.25 in. (3.18 cm) Head Diameter at Tri-Lobe Anti-Roll Flange: 1.44 in. (3.66 cm)
Barrel Diameter: 0.95 in. (2.41 cm)

Weight: 5.22 oz (148 grams) with battery

Lens: Borofloat High Temperature Glass

Light Source: C4® LED technology, impervious to shock with a 50,000 hour lifetime.

On/Off: Multi-function, push-button tactical tailswitch. One handed operation of momentary, variable intensity or strobe mode.

Battery: Lithium Ion with on-board safety control circuit, 3.75V, 2000mAh minimum, rechargeable up to 500 times.

Charging: Fits existing Strion® chargers. Clamp style charge holder with digital control circuit that prevents over charge. Fully recharges battery in 3 hours. Charges battery in product. Charge base LED indication: LED Steady – Charging; LED Blinking – Charged.

- Features:
- C4 LED technology for extreme brightness
 - LED Charge-continuity indicator on charger base; Compact, snap-in charger mounts in any position
 - IPX4 rated design; water resistant operation
 - Serialized for positive identification

Approvals: Most models meet applicable European Community Directives.

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

| Description | Item # | UPC |
|--------------------------------------|--------|----------------|
| Strion LED with 230V AC/DC 1 Holder | 74311 | 080926-74311-3 |
| Strion LED with 240V AC/DC 1 Holder | 74321 | 080926-74321-2 |
| Strion LED with 120V AC/DC 1 Holder | 74301 | 080926-74301-4 |
| Strion LED with 100V AC/DC 1 Holder | 74331 | 080926-74331-1 |
| Strion LED with 230V AC/DC 2 Holders | 74312 | 080926-74312-0 |
| Strion LED with 240V AC/DC 2 Holders | 74322 | 080926-74322-9 |
| Strion LED with 120V AC/DC 2 Holders | 74302 | 080926-74302-1 |
| Strion LED with 100V AC/DC 2 Holders | 74332 | 080926-74332-8 |

| Description | Item # | UPC |
|-------------------------|--------|----------------|
| Strion LED with 230V AC | 74313 | 080926-74313-7 |
| Strion LED with 240V AC | 74323 | 080926-74323-6 |
| Strion LED with 120V AC | 74303 | 080926-74303-8 |
| Strion LED with 100V AC | 74333 | 080926-74333-5 |
| Strion LED with DC | 74304 | 080926-74304-5 |
| Strion LED (W/OCHARGER) | 74300 | 080926-74300-7 |

Additional part numbers on reverse





| Item | | UPC | Part # |
|---|------------------|----------------|--------|
| DC2 direct wire charge cord | | 080926-22050-8 | 22050 |
| DC1 Charge Cord | | 080926-22051-5 | 22051 |
| 120V AC charge cord | | 080926-22311-0 | 22311 |
| 100V AC charge cord | | 080926-22666-1 | 22666 |
| 230V AC charge cord | | 080926-22664-7 | 22664 |
| 240V AC charge cord | | 080926-22241-0 | 22241 |
| Charger Holder | | 080926-74102-7 | 74102 |
| Battery Stick (Li-Ion) | | 080926-74175-1 | 74175 |
| Rail Mount | | 080926-74200-0 | 74200 |
| Vertical Grip with Rail - machined aluminum, ambidextrous hard anodized rail grabber vertical foregrip with integral Picatinny rail and storage compartment | | 080926-69114-8 | 69114 |
| 6-unit Bank Charger 120V AC | | 080926-74400-4 | 74400 |
| 6-unit Bank Charger 230V AC | | 080926-74600-8 | 74600 |
| 6-unit Bank Charger 100V AC | | 080926-74700-5 | 74700 |
| 6-unit Bank Charger 12V DC | | 080926-74401-1 | 74401 |
| Safety Wand | Red | 080926-74903-0 | 74903 |
| Safety Wand | Yellow | 080926-74904-7 | 74904 |
| Safety Wand | Glow in the dark | 080926-74913-9 | 74913 |
| Flip Lens | I/R | 080926-74039-6 | 74039 |
| Flip Lens | Red | 080926-85115-3 | 85115 |
| Flip Lens | Blue | 080926-85116-0 | 85116 |
| Flip Lens | Green | 080926-85117-7 | 85117 |
| Black nylon holster | | 080926-85905-0 | 85905 |
| Black leather holster - plain | | 080926-74059-4 | 74059 |
| Black leather holster - basket weave pattern | | 080926-74060-0 | 74060 |