


Torpedos

Globes

T-Capsules


Item Number	ENERGY STAR®	Item Description	Unit/Ballast Watts	Incandescent Comparison (Watts)	Initial Lumens	CCT (Kelvin)	CRI	MOL/Height (Inches)	Diameter/Width (Inches)	Base Type	Case Quantity
-------------	--------------	------------------	--------------------	---------------------------------	----------------	--------------	-----	---------------------	-------------------------	-----------	---------------

TORPEDO LAMP, ELECTRONIC, NPF, 8,000 HOUR




10704	★	4 Watt Torpedo	4	15	195	2700	82	4.4	1.4	E26	12
10704C	★	4 Watt Torpedo CAND	4	15	195	2700	82	4.4	1.4	E12	12
10709	★	9 Watt Torpedo	9	40	425	2700	82	4.8	1.7	E26	12
10709C		9 Watt Torpedo Lamp	9	40	425	2700	82	4.8	1.7	E12	12
10714		14 Watt Torpedo Lamp	14	60	720	2700	82	5.4	1.7	E26	12
10714C		14 Watt Torpedo Lamp CAND	14	60	720	2700	82	5.4	1.7	E12	12

GLOBE LAMP, ELECTRONIC, 8,000 HOUR



1G2004		4 Watt G20 Globe	4	25	250	2700	82	3.6	2.5	E26	12
1G2004C		4 Watt G20 Globe CAND	4	25	210	2700	82	3.6	2.5	E12	12
1G2504	★	4 Watt G25 Globe	4	25	250	2700	82	4.0	3.1	E26	6
1G2504C		4 Watt G25 Globe CAND	4	40	250	2700	82	4.0	3.1	E12	6
1G2509	★	9 Watt G25 Globe	9	40	520	2700	82	4.4	3.1	E26	6
1G2509C		9 Watt G25 Globe CAND	9	40	520	2700	82	4.4	3.1	E12	6
2G2514	★	14 Watt G25 Globe	14	60	800	2700	82	4.4	3.1	E26	6
1G3009		9 Watt G30 Globe	9	40	520	2700	82	5.0	3.7	E26	6
1G3014	★	14 Watt G30 Globe	14	60	800	2700	82	5.0	3.7	E26	6
1G3019	★	19 Watt G30 Globe	19	75	1100	2700	82	5.0	3.7	E26	6
1G3023		23 Watt G30 Globe	23	100	1200	2700	82	5.9	3.7	E26	6
1G4014	★	14 Watt G40 Globe	14	60	800	2700	82	6.8	5.0	E26	6
1G4019	★	19 Watt G40 Globe	19	75	1100	2700	82	6.8	5.0	E26	6
1G4023		23 Watt G40 Globe	23	100	1300	2700	82	6.8	5.2	E26	6

T-CAPSULE LAMP, ELECTRONIC, 8,000 HOUR



1T2014	★	14 Watt T20 Capsule	14	60	800	2700	82	5.4	2.5	E26	12
1T2414	★	14 Watt T24 Capsule	14	60	900	2700	82	5.2	3.5	E26	6
1T2419	★	19 Watt T24 Capsule	19	75	1100	2700	82	5.6	3.5	E26	6
1T2423		23 Watt T24 Capsule	23	100	1200	2700	82	6.3	3.5	E26	6