

Universal Boxes and Covers

Deep Boxes — Single-Gang

CAT. NO.	HUB SIZE (IN.)	OUTLETS
Three Outlets		
IHD3-1•	½	Top 1
IHD3-2•	¾	Bottom 1
IHD3-3•	1	Back 1
		TOTAL 3



CAT. NO.	HUB SIZE (IN.)	OUTLETS
Four Outlets		
IHD4-1•	½	Top 2
IHD4-2•	¾	Bottom 1
		Back 1
		TOTAL 4



CAT. NO.	HUB SIZE (IN.)	OUTLETS
Two-Gang Five Outlets		
2IHD5-1•	½	Top 2
2IHD5-2•	¾	Bottom 2
2IHD5-3•	1	Back 1
		TOTAL 5




CAT. NO.	HUB SIZE (IN.)	OUTLETS
Three-Gang Seven Outlets		
3IHD7-2•	¾	Top 3
3IHD7-3•	1	Bottom 3
		Back 1
		TOTAL 7



Close-Up Plugs — Zinc

CAT. NO.	COLOR	HUB SIZE (IN.)
PLG-1-RD	Silver	½
PLG-2-RD	Silver	¾
PLG-3-RD	Silver	1



D-PAK®

CAT. NO.	COLOR	HUB SIZE (IN.)
DPLG-1	Silver	½
DPLG-1-BR	Bronze	½
DPLG-1-WH	White	½
DPLG-2	Silver	¾

Extensions — Single-Gang

CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
No Outlets — 1" Deep			
IHE	N/A	0	Extension Ring for One-Gang Box with Gasket and Screws



CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Four Outlets — 1½" Deep			
IHE4-1	½	Top 2	4-Hole Extension Ring for One-Gang Box with 4 Plugs, Gasket and Screws
		Bottom 2	
		TOTAL 4	



CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Two Outlets, Flanged — 1½" Deep Add-On			
IHEF2-1	½	Top 1	2-Hole Flanged Box Extension Adapter with 1 Plug Gasket and Screws
IHEF2-2	¾	Bottom 1	
		TOTAL 2	



CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Six Outlets, Flanged — 1½" Deep Add-On			
IHEF6S2-1	½	Top 2	6-Hole Flanged Box Extension Adapter with 4 Plugs, Gasket and Screws
IHEF6S2-2	¾	Bottom 2	
LTX100-5	1	Side 1	
		Side 1	
		TOTAL 6	



Two-Gang

CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Deep			
2IHE	N/A	0	Extension Ring for Two-Gang Boxes with Gasket and Screws



Round

CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Four Outlets — 1½" Deep			
SE-47	½	4	Round Extension with Gasket and Screws
SE-48	¾	4	




Mounting Lugs

CAT. NO.	DESCRIPTION
LM	2 Mounting Lugs with Self-Tapping Screws, for LM Boxes Only




Universal Boxes and Covers

Single-Gang Boxes




Single-Gang Extension Rings



Two-Hole Flanged Box Extension Adapter


Six-Hole Flanged Box Extension Adapter




Single-Gang Boxes

CAT. NO.	HUB SIZE	DIMENSIONS (IN.)									
		A	B	C	D	E	F	G	H	J	CI
IH-1	1/2	4 1/16	2 13/16	2	5/8	—	—	3/4	1 1/8	1 1/2	17.3
IH-2	3/4	4 1/16	2 13/16	2	5/8	—	—	3/4	1 1/8	1 1/2	17.0
IH-LM-1	1/2	4 1/16	2 13/16	2	5/8	3 13/16	3 1/2	3/4	1 1/8	1 1/2	17.3
IH-LM-2	3/4	4 1/16	2 13/16	2	5/8	3 13/16	3 1/2	3/4	1 1/8	1 1/2	17.0
IH-S-1	1/2	4 1/16	2 13/16	2	5/8	3 13/16	3 1/2	3/4	1 1/8	1 1/2	17.0
IH-S-2	3/4	4 1/16	2 13/16	2	5/8	3 13/16	3 1/2	3/4	1 1/8	1 1/2	17.0
IHD-1	1/2	4 1/16	2 13/16	2 5/8	5/8	3 13/16	3 1/2	3/4	1 1/8	1 1/2	24.8
IHD-2	3/4	4 1/16	2 13/16	2 5/8	5/8	3 13/16	3 1/2	3/4	1 1/8	1 1/2	24.8
IHD-3	1	4 1/16	2 13/16	2 5/8	3/4	3 13/16	3 1/2	3/4	1 1/8	1 1/2	23.5

Two- and Three-Gang Boxes



Two-Gang Extension Ring



Two- and Three-Gang Boxes

CAT. NO.	DIMENSIONS (IN.)												
	A	B	C	D	E	F	G	H	J	K	L	M	CI
2IH3	4 1/16	4 3/8	2 1/16	5/8	5	3 1/2	3 13/32	3 3/4	—	—	3/4	3 3/16	31.8
2IH4	4 1/16	4 3/8	2 1/16	5/8	5	3 1/2	3 13/32	3 3/4	1 1/2	—	3/4	3 3/16	31.8
2IH5	4 1/16	4 3/8	2 1/16	5/8	5	3 1/2	3 13/32	3 3/4	1 1/2	—	3/4	3 3/16	31.8
2IH5S2	4 1/16	4 3/8	2 1/16	5/8	5	3 1/2	3 13/32	3 3/4	—	—	3/4	3 3/16	31.8
2IH7	4 1/16	4 3/8	2 1/16	5/8	5	3 1/2	3 13/32	3 3/4	—	1 1/2	3/4	3 3/16	30.3
2IH7S2	4 1/16	4 3/8	2 1/16	5/8	5	3 1/2	3 13/32	3 3/4	1 1/2	—	3/4	3 3/16	32.0
2IHD5	4 1/16	4 3/8	2 13/32	3/4	5	3 1/2	3 13/32	3 3/4	1 3/16	—	3/4	3 3/16	40.3
3IHD7	4 1/16	6 1/16	2 13/32	1 1/16	6 13/16	3 1/2	3 3/4	5 5/8	—	1 1/16	3/4	3 3/16	54.8