

Universal Boxes and Covers

Deep Boxes — Single-Gang

CAT. NO.	HUB SIZE (IN.)	OUTLETS
Three Outlets		
IHD3-1•	½	Top 1
IHD3-2•	¾	Bottom 1
IHD3-3•	1	Back 1
		TOTAL 3



CAT. NO.	HUB SIZE (IN.)	OUTLETS
Four Outlets		
IHD4-1•	½	Top 2
IHD4-2•	¾	Bottom 1
		Back 1
		TOTAL 4



CAT. NO.	HUB SIZE (IN.)	OUTLETS
Two-Gang Five Outlets		
2IHD5-1•	½	Top 2
2IHD5-2•	¾	Bottom 2
2IHD5-3•	1	Back 1
		TOTAL 5




CAT. NO.	HUB SIZE (IN.)	OUTLETS
Three-Gang Seven Outlets		
3IHD7-2•	¾	Top 3
3IHD7-3•	1	Bottom 3
		Back 1
		TOTAL 7



Close-Up Plugs — Zinc

CAT. NO.	COLOR	HUB SIZE (IN.)
PLG-1-RD	Silver	½
PLG-2-RD	Silver	¾
PLG-3-RD	Silver	1



D-PAK®

CAT. NO.	COLOR	HUB SIZE (IN.)
DPLG-1	Silver	½
DPLG-1-BR	Bronze	½
DPLG-1-WH	White	½
DPLG-2	Silver	¾

Extensions — Single-Gang

CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
No Outlets — 1" Deep			
IHE	N/A	0	Extension Ring for One-Gang Box with Gasket and Screws



CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Four Outlets — 1½" Deep			
IHE4-1	½	Top 2	4-Hole Extension Ring for One-Gang Box with 4 Plugs, Gasket and Screws
		Bottom 2	
		TOTAL 4	



CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Two Outlets, Flanged — 1½" Deep Add-On			
IHEF2-1	½	Top 1	2-Hole Flanged Box Extension Adapter with 1 Plug Gasket and Screws
IHEF2-2	¾	Bottom 1	
		TOTAL 2	



CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Six Outlets, Flanged — 1½" Deep Add-On			
IHEF6S2-1	½	Top 2	6-Hole Flanged Box Extension Adapter with 4 Plugs, Gasket and Screws
IHEF6S2-2	¾	Bottom 2	
LTX100-5	1	Side 1	
		Side 1	
		TOTAL 6	



Two-Gang

CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Deep			
2IHE	N/A	0	Extension Ring for Two-Gang Boxes with Gasket and Screws



Round

CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Four Outlets — 1½" Deep			
SE-47	½	4	Round Extension with Gasket and Screws
SE-48	¾	4	



Mounting Lugs

CAT. NO.	DESCRIPTION
LM	2 Mounting Lugs with Self-Tapping Screws, for LM Boxes Only

