

Connector Kits

Connector Kit for Copper Cables

CAT. NO.	DESCRIPTION	STD. PKG.	WT. EACH
TBM2K-1	Color-Keyed® Connector Kit	1	12

Kit Includes

CAT. NO.	ITEMS	CABLE SIZE		QTY.
54104	One-Hole Lugs	#8		25
54105	One-Hole Lugs	#6		25
54106	One-Hole Lugs	#4		15
54107	One-Hole Lugs	#2, #3		10
54504	2-Way Splice Connectors	#8		15
54505	2-Way Splice	#6		15
54506	2-Way Splice	#4		10
54507	2-Way Splice	#2		5
		MIN.	MAX.	
54610	Pigtails	3-#12	#4-#12	15
54615	Pigtails	#4-#12	#4-#10	15
54620	Pigtails	#3-#8	#1-#4	15
		#10	#10	
54710	C-Taps	#8	#12	15
		#6	#10-#12	
54615	C-Taps	#8	#8-#10	15
		#4 or #5	#8-#10-#12	
54720	C-Taps	#6	#6-#8	
TBM20S OR TBM45S	Manual Crimp Tool	#8	#2	1

UL not applicable



Carrying Cases

MDPWK12 Case Contents

(1) PWK1	(10) MD1210F-1	(6) MD8M-2	(6) MD8F-2	(30) B00T-1
(10) MD1210M-1	(10) MD8F-1	(6) MD6M-2	(6) MD6F-2	(6) MD1210M-2
(10) MD8M-1	(10) MD6F-1	(6) MD4M-2	(6) MD4F-2	(6) MD1210F-2
(10) MD6M-1	(30) MDB00T-2	(6) MD2M-2	(6) MD2F-2	

MDPWK23 Case Contents

(1) PWK1	(6) MD1210F-2	(3) MD2M-3	(3) MD2F-3	(6) MD1M-2
(6) MD1210M-2	(6) MD8F-2	(3) MD1M-3	(3) MD1F-3	(36) MDB00T-2
(6) MD8M-2	(6) MD6F-2	(3) MD10M-3	(3) MD10F-3	(18) MDB00T-3
(6) MD6M-2	(6) MD4F-2	(3) MD20M-3	(3) MD20F-3	
(6) MD4M-2	(6) MD2F-2	(3) MD30M-3	(3) MD30F-3	
(6) MD2M-2	(6) MD1F-2	(3) MD40M-3	(3) MD40F-3	

MDKITL Case Contents

(1) PWK1	(1) TBM25S	(24) MDB00T-2	(3) M2D2M-2	(6) MD8M-1
(3) M2D4M-2	(3) M2D6M-2	(3) M2D8M-2	(12) M2DB00T-2	(6) MD8F-1
(12) MDB00T-1	(12) MD2F-2	(12) MD4F-2	(12) MD6F-2	(6) MD8M-2
(12) M2D8F-2	(6) MD2M-2	(6) MD4M-2	(6) MD6M-2	(6) MD6M-1
(6) MD6F-1				

CAT. NO.	DESCRIPTION
PWK1	Empty case — includes wall chart; make up your own selection of Blackburn® lugs, splices, taps or motor disconnects featuring the Color-Keyed® system.
PWK4	Metal cabinet that holds four of the PWK1 shells that slide out for easy removal.
MDPWK12	Selection of size 1 and 2 male and female motor disconnects plus insulators; to connect 60 single line to single load motor leads, #12 AWG through #2 AWG; tools not included.
MDPWK23	Selection of size 2 and 3 male and female motor disconnects plus insulators; to connect 54 single line to single load motor leads, #12 AWG through #4/0 AWG; tools not included. Size 2 and 1 male and female motor disconnects plus insulators; to convert single to single line or single line to two line.
MDKITL	Includes Tool.



MDKITL