



PROFESSIONAL

10 oz. "9" LITTLE PRO®

A beautifully balanced small hammer, ideal for cabinet making and finishing work. Top quality white hickory handle is triple wedged.

ITEM CODE	CATALOG NO.	HEAD WEIGHT oz.	g	LGTH. in.	STD. PKG.	PKG. lbs.
122-01	9	10	285	11	4	4
122-12	9-D 6 PIECE COUNTER DISPLAY (see back cover)					

16 oz. "99" PRO-16®

Available with either smooth or milled face, this is a nicely proportioned hammer for all-round use. Top quality, white hickory handle is triple wedged.

ITEM CODE	CATALOG NO.	HEAD WEIGHT oz.	g	LGTH. in.	STD. PKG.	PKG. lbs.
124-00	99	16	450	13	4	6
Milled Face						
124-20	MS99	16	450	13	4	6

20 oz. "999" FRAMING

Available in two lengths, with either smooth or milled face, its superb balance and comfortable grip make this hammer a favorite of tradesmen. Top quality, white hickory handle is triple wedged.

ITEM CODE	CATALOG NO.	HEAD WEIGHT oz.	g	LGTH. in.	STD. PKG.	PKG. lbs.
105-00	999	20	570	14	4	7¼
105-10	999L	20	570	16	4	7¼
Milled Face						
105-20	999M	20	570	14	4	7¼
105-30	999ML	20	570	16	4	7¼
105-37	999MLFO	20	570	16	4	7¼



505M



606M



707M

RIP HAMMERS

24 oz. "505" FRAMING

Available with either smooth or milled face, this framing hammer sets the industry standard for appearance and balance. Top quality white hickory handle is triple wedged.

ITEM CODE	CATALOG NO.	HEAD WEIGHT oz.	g	LGTH. in.	STD. PKG.	PKG. lbs.
123-01	505	24	680	17	4	9
Milled Face						
123-20	505M	24	680	17	4	9

28 oz. 606M SUPER FRAMING

An extra-heavy framer designed to provide excellent overall balance. Top quality white hickory handle is triple-wedged. Milled face.

ITEM CODE	CATALOG NO.	HEAD WEIGHT oz.	g	LGTH. in.	STD. PKG.	PKG. lbs.
106-20	606M	28	800	18	2	4¾
Lineman's Straight Claw - Smooth Face - 15" Hickory Handle						
106-02	606S	28	800	15	2	4½

32 oz. 707M SUPER FRAMING

The heaviest framer you can buy, yet proportioned to give excellent balance. Milled face. The top quality, white hickory handle is triple-wedged.

ITEM CODE	CATALOG NO.	HEAD WEIGHT oz.	g	LGTH. in.	STD. PKG.	PKG. lbs.
107-20	707M	32	900	18	2	5½
Smooth Face						
107-01	707	32	900	18	2	5½



Handle triple-wedged to head.

Special deep-throat design for power strikes in difficult areas

Extra-large striking face for surer strikes



Optional milled face helps prevent glancing blows and flying nails