



## Metal Clad Cable Termination Fittings & Accessories

**T&B Catalog Number:**

ST075-468

**UPC Number:**

78621071287

**Status:**

Active

**Description:**

Star Teck aluminum jacketed cable fitting hub size 3/4 inch Range over jacket 1.025-1.205 inches.

### Features

Easy Installation-Exclusive power-grip. Provides a grip that's high up on the cable-not on the first convolution-so strip length and cutting of cable are not critical.

Dependable Service-stainless steel retaining ring. Withstands corrosive environments. Non-magnetic.

Dependable Grounding-Power-Grip grounding ring is non-magnetic stainless steel. Provides 360°; long-term dependable grounding. It makes immediate contact with the cable.

Watertight-Tapered bushing. Cone shaped to provide a secure, tight fit while eliminating cupping or water in vertical installations.

Easy to Install In Tight Spaces-Low profile glad nut fits tight spaces. Has grooves for screwdriver installation, and flats for a wrench. Durable and reusable with funnel entry for easy cable insertion.

### Application

Provides means for passing armored, metal clad, jacketed cable through a bulkhead or enclosure in hazardous areas. (these fittings are suitable for hazardous areas when used with T&B sealing compound).

Form a mechanical grip and water and/or oil-resistant termination.

Provide grounding continuity of cable armor.

### General

Material Aluminum

### Dimension Information

Hub Size (inches)	3/4
Dimension A (inches)	0.819
Dimension B (inches)	2.450
Dimension C (inches)	2.080
Range Over Jacket -Minimum (inches)	1.025
Range Over Jacket -Maximum (inches)	1.205
Range Over Armor -Minimum (inches)	0.915
Range Over Armor -Maximum (inches)	1.125

### Specifications

3dmodel Available on Website

### Packaging

Package in Units	20
T&B Sold in UOM	Each
T&B Weight Per UOM	36.17 lbs. per 100

## Application Support

T&B Instruction Sheets	ta00904-tb2
Product Specifications & Overview	Available on Website

## Certifications

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:  
E 38947

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com